

Type 0ADKC / 0ADKP

Time-Delay, Ceramic Tube Fuse Series

HF **Pb** 0ADKC/0ADKP Series, 5x20mm Ceramic Tube Time-Delay Fuse

RoHS Compliant

Description

600Vac / 500Vdc rated ceramic tube cartridge fuse in a compact 5 x 20mm Package.

Features

- Time-delay, high breaking capacity
- Ceramic tube, Silver plated copper cap construction
- Available in cartridge and pigtail axial lead
- Full compliance with EU Directive 2011/65/EU and amending directive 2015/863
- Halogen Free
- Lead Free



Applications

- Industrial Power Supplies
- DC/DC modules

LEAD FREE = **Pb**

HALOGEN FREE = **HF**

Physical Specifications

Materials	Body : Ceramic
	Cap : Silver Plated Copper Alloy
	Pigtail Leads : Tin Plated Copper
Marking	On Fuse :
	"bel"
	"0ADK", "Current Rating", "Voltage Rating", "Appropriate Safety Logos"
	On Label :
	"bel", "0ADKC" or "0ADKP", "Current Rating", "Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and "  ", "  "(China RoHS compliant).

Safety Agency Approvals

Safety Agency	Safety Agency Certificate	Ampere Rating / Voltage Rating	Ampere Range / Volt @ I.R. ability*
	E20624	500mA-20A/600V AC 500mA-20A/500V DC 500mA-10A/400V DC	500mA-20A/600V@200A AC 500mA-20A/500V@300A DC 500mA-10A/400V@2KA DC
	B 058849 0020	1A-16A/500V AC/ DC	1A-10A/500V@500A AC 12A-16A/500V@200A AC 1A-16A/500V@ 1KA DC

*I.R.= Interrupting Rating = Short Circuit Rating(Amps)

Electrical Characteristics

Rated Current	1.5In	2.1In	2.75In	3.0In	4.0In	10.0In
<1A	1 hour min.	N/A	N/A	120sec max	N/A	N/A
1A-3.15A	1 hour min.	30min. max.	750ms-80sec	N/A	95ms-5sec	10ms-150ms
4A-6.3A	1 hour min.	30min. max.	750ms-80sec	N/A	150ms-5sec	10ms-150ms
8A-20A	30min. min	30min. max.	750ms-80sec	N/A	150ms-8sec	10ms-150ms

Environmental Specifications

Operating Temperature	-40°C to +125°C
Terminal Strength	MIL-STD-202G, Method 211 Test Condition A
Lead Solderability	MIL-STD-202, Method 208
Mechanical Vibration	MIL-STD-202, Method 201
Thermal Shock	MIL-STD-202, Method 107 Test Condition B (5 cycles -65°C to +125°C)
Humidity	MIL-STD-202, Method 103, Test Condition A (95%RH and 40°C for 240 hours)

Electrical Specifications


Part Number	Ampere Rating	Typical Cold Resistance (mOhms)	Voltage and Interrupting Ratings	Typical Voltage Drop (mV)	Typical Pre –Arcing I²t (A² Sec)	Agency Approvals	
							
0ADKC0500-XX	500mA	382	See Table of Ratings on Page 1 for Voltage and associated Interrupting Ratings	190	0.287	Y	
0ADKP0500-XX							
0ADKC0630-XX	630 mA	359		261	0.34	Y	
0ADKP0630-XX							
0ADKC0800-XX	800mA	175		144	1.18	Y	
0ADKP0800-XX							
0ADKC1000-XX	1A	210		250	1.4	Y	Y
0ADKP1000-XX							
0ADKC1250-XX	1.25A	134		138	2.34	Y	Y
0ADKP1250-XX							
0ADKC1600-XX	1.6A	100		180	3.9	Y	Y
0ADKP1600-XX							
0ADKC2000-XX	2A	65		158	9.4	Y	Y
0ADKP2000-XX							
0ADKC2500-XX	2.5A	34		93	12.5	Y	Y
0ADKP2500-XX							
0ADKC3150-XX	3.15A	28		110	17.8	Y	Y
0ADKP3150-XX							
0ADKC4000-XX	4A	24		118	25	Y	Y
0ADKP4000-XX							
0ADKC5000-XX	5A	17		104	50	Y	Y
0ADKP5000-XX							
0ADKC6300-XX	6.3A	13		100	80	Y	Y
0ADKP6300-XX							
0ADKC8000-XX	8A	9		85	179	Y	Y
0ADKP8000-XX							
0ADKC9100-XX	10A	7.6		90	400	Y	Y
0ADKP9100-XX							
0ADKC9120-XX	12A	6		80	576	Y	Y
0ADKP9120-XX							
0ADKC9150-XX	15A	4.3		75	900	Y	Y
0ADKP9150-XX							
0ADKC9160-XX	16A	3.7		68	1024	Y	Y
0ADKP9160-XX							
0ADKC9200-XX	20A	2.7		65	2400	Y	
0ADKP9200-XX							

Consult manufacturer for other ratings


*DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25°C

*Typical Pre-arcing I²t are measured at 10In Current

Temperature Re-Rating Curve



Average Time Current Curve



Soldering parameters for Pigtail Type

Wave Soldering Compatible: (260°C, 10 sec max)

Hand-Solder:

Solder Iron Temperature: (350°C +/- 5°C)

Heating Time: (5 sec max)

Type 0ADKC /0ADKP

4 / 4

Fuse FGNO Explanation


0ADK X [XXXX] -XX

0ADKC/P=0ADKC/P; [XXXX]=Ampere Rating; XX=See Ordering Information as below

Fraction	Decimal	Milliamps	Bel FGNO[XXXX]
1/2	0.500	500	0500
	.630	630	0630
8/10	.800	800	0800

Fraction	Decimal	Amps	Bel FGNO[XXXX]
	1.0	1	1000
1-1/4	1.25	1.25	1250
	1.6	1.6	1600
	2.0	2	2000
2-1/2	2.5	2.5	2500
	3.15	3.15	3150
	4.0	4	4000
	5.0	5	5000
	6.3	6.3	6300
	8.0	8	8000
		10	9100
		12	9120
		15	9150
		16	9160
		20	9200

Mechanical Dimensions



Ordering Information

0ADK X XXXX - X X

FUSE TYPE _____
 0ADK

MOUNTING TAB STYLE _____
 C = For Cartridge version
 P = For Axial lead pigtail

AMPERE RATING _____
 Refer to fuse FGNO explanation table

PACKAGING CODE _____
 A = Ammo (10mm Pitch and 52mm & Pigtail length 16mm)
 B = Bulk (Cartridge version)
 R = Bulk (Pigtail length 38mm)

QUANTITY CODE _____
 E = 1000 / box
 P = 1000 / box (ammo pack)

Packaging

Packaging Option	Quantity	Packaging Code	Inside Tape Spacing
Bulk (Cartridge Type)	1000	BE	N/A
Bulk (Pigtail Type)	1000	RE	N/A
Box (Pigtail Type)	1000	AP	10mm Pitch and 52mm



Specifications subject to change without notice

Bel Fuse Inc.
 300 Executive Drive, Suite 300,
 West Orange, NJ 07052 USA

+1 201.432.0463
 Bel.US.CS@belf.com
belfuse.com/circuit-protection

© 2025 Bel Fuse, Inc.

Rev. 0ADKC/0ADKP Oct2025