







Notes:

Material:

Shell: Mat'l- Steel.

Finish: Nickel Plate

Insulator: PBT

Contacts: Brass

Finish:

Contact Area: Gold Plate over Nickel Plate
on Solder Tail: Tin Plate over Nickel Plate

Electrical Specifications

Rated Voltage: 30V AC (rms)

Contact Current Rating: 1 A Max.

Contact Resistance: 30 milliohms Max.

Dielectric Withstanding: 500V AC

Operating Temperature: -55°C to 85°C

6.16.25	CHANGE AS PER PCN 25-031. SHELL MAT'L WAS BRASS.	L
5.07.25	(K1) WAS .084 [2.14] UPDATED MOUNTING DETAILS	K
3.20.25	UPDATED MAT'L&MOUNTING DETAILS. CHANGE AS PER ECN 25-087.	J

DATE	DESCRIPTION	REV.
------	-------------	------

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500			
PART NAME			
USB A-TYPE VERTICAL SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	6.18.98
		APP'D	SCALE
		RH	2.5X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	± .010 [± 0.25]	C	923
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			