



| ▲ O.P. (MM) | P.T. (MM) |
|-------------|-----------|
| 19.0±1.5    | 5.2 MAX.  |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4  
X.XX=± 0.25
3. RATING: 15A @125/250VAC UL, CUL APPROVED
- ▲ 4. OPERATING FORCE: 140± 40 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.



| REV | ECO NO     | DESCRIPTION                | DATE     | BY | E-SWITCH®              |          |    |         | OBJECT ID |
|-----|------------|----------------------------|----------|----|------------------------|----------|----|---------|-----------|
| C   | ECO-100816 | REMOVE VDE RATING AND LOGO | 03/30/22 | JS | TITLE LS0851504F140C1A |          |    |         | 000020998 |
|     |            |                            |          |    | SCALE                  | DATE     | DR | DWG     | REV       |
|     |            |                            |          |    | 3:2                    | 7/6/2005 | JB | Q950010 | C         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED