




FRONT SHELL









INSERTED BODY



REAR SHELL



ASSEMBLED PLUG



PLUG SPECIFICATIONS:

SHELL: MAT'L- STEEL

FINISH- NICKEL PLATE

INSULATION: MAT'L- THERMOPLASTIC, UL 94V-0

CONTACT: MAT'L- PHOSPHOR BRONZE

FINISH- GOLD FLASH OVER NICKEL

ELECTRICAL CHARACTERISTICS:

RATED VOLTAGE: 30V (RMS)

CONTACT CURRENT RATING: 1 Amp DC MAX.

CONTACT RESISTANCE: 15m Ω min.

DIELECTRIC WITHSTANDING VOLTAGE: 750V AC FOR 1 MINUTE

MECHANICAL CHARACTERISTICS:

OPERATING TEMPERATURE: -13°F (-25°C) TO 176°F (+80°C)

DURABILITY: 1500 CYCLES MIN.

PACKAGING DETAILS: 100 PIECES PER BAG.

DATE	DESCRIPTION	REV.
5.23.16	CHANGE AS PER ECN 16-060	A
2.25.25	CHANGE AS PER PCN 25-011.	B
	ADDED PACKAGING DETAILS.	

www.keystelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500			
PART NAME			
USB 3.0 TYPE B PLUG KIT			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		NT	4.07.10
TOLERANCES		APPD	SCALE
DECIMAL ± .010 [± 0.25]		RH	2X
ANGULAR ± 1°		DWG NO.	
UNLESS OTHERWISE SPECIFIED		C	
952			

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.