


O.P. (MM)	P.T. (MM)
20.7 ± 1.5	5.5 MAX.





O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPST
NORMALLY CLOSED

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 0.4VA @ 20 VDC or VAC Max.
- ▲ 4. OPERATING FORCE: 120 $\pm$ 40 GRAMS
5. OPERATING TEMP: -25°C to 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS Max.
11. ▲ DENOTES CRITICAL PARAMETER
- ▲ 12. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (P/N Q990000)



REV	ECO NO	DESCRIPTION	DATE	BY	 OBJECT ID 000021048				
C	ECO-102147	P.T. 5.5 MAX WAS 4.0 AND ADD NOTE 12	08/10/23	JS					
					TITLE LS085R106F120C1B				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 3:2	DATE 8/18/2008	DR BLR	DWG Q950061	REV C