



PANEL THICKNESS	X
0.75-1.25	19.2
1.25-2.00	19.4
2.00-3.00	19.8

RECOMMENDED
PANEL CUT-OUT



▲ OFF-ON
SPST

SCHEMATIC



▲ LENS COLOR:
BLUE



▲ 4B
CUT TERMINAL

▲ RUBBER COLOR:
WHITE

10.40
[.409 in]

▲ LENS STYLE:
FULL ILLUMINATION

BODY COLOR:
WHITE

15.00
[.591 in]

▲ 1.8
[.071 in]

24.50
[.965 in]

Ø1.70
[.067 in]

▲ 6.30
[.248 in]

.80
[.031 in]

11.20 ± .50
[.441 ± .020 in]

12.00 ± .50
[.472 ± .020 in]

18.80
[.740 in]

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X ± 0.4
X.XX ± 0.25
3. ELECTRICAL LIFE: 6,000 [cURus]
4. CONTACT RESISTANCE: 20 mΩ MAX. INITIAL
5. INSULATION RESISTANCE: 100 MΩ AT 500VDC
6. OPERATING TEMPERATURE: -20°C TO +65°C [cURus]
7. CONTACT RATING: 16A, 125VAC-250VAC, [cURus]
8. DIELECTRIC STRENGTH: 1000V FOR 1 MINUTE
- ▲ 9. ILLUMINATION VOLTAGE: 12V
10. ▲ DENOTES CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-100489	REMOVE VDE FROM NOTES	12/13/21	JS	TITLE PA4R11C2021-144				000000232
					SCALE	DATE	DR	DWG	REV
					2:1	10/17/2011	BGL	14-PA4R11C2021144	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED