





Technical drawing of a mechanical assembly, likely a pump or motor component, shown in a side view. The drawing includes a coordinate grid with dimensions 16, 15, 14, 13, 12 along the top and 16, 15, 14, 13, 12 along the right side. The assembly consists of a main body with a central shaft and a flange. Callouts 4 and 6 point to specific features on the flange. Callout 4 points to the top surface of the flange, and callout 6 points to the bottom surface of the flange. The drawing is labeled with 'M', 'L', 'K', 'J', and 'H' along the left edge.



CRIMP TOOLING ACC. DELPHI PROCESSING SPEZIFIKATION
CRIMP WERKZEUGE GEMAESS DELPHI VERARBEITUNGSSPEZIFIKATION
TO BE USED ON TAB 2,8^{+0,3}_{-0,1} x 0,8 ± 0,03
GEEIGNET FUER FLACHSTECKER 2,8^{+0,3}_{-0,1} x 0,8 ± 0,03
DEAD END PLUG DELPHI NO. 12337197 (COLOUR WHITE)
BLINDSTOFFEN DELPHI NR. 12337197 (FARBE WEISS)

- | KEY PRODUCT CHARACTERISTICS | | | | | |
|---|-------------|---|--|------------------|------|
|  SAFETY/COMPLIANCE | |  FIT/FUNCTION | | TOTAL ON DRAWING | 0 |
|  S/C CHECKPOINTS | |  R/F CHECKPOINTS | | LAST NO. USED | 0 |
| NO & TYPE | DESCRIPTION | RATIONALE | | PTS | ZONE |
| | | | | | |

DIMENSIONAL RANGE (MM)		CHART D
FROM	0	> 12
	12	
TOLERANCE UNLESS OTHERWISE SPECIFIED		
	±0.1	±0.2
ANGULAR TOLERANCE ±2°		

USE MATH DATA	U	N
3		

16	15	14	13	12
----	----	----	----	----