





▲ SWITCH FUNCTION

| POS. 1 | POS. 2 |
|--------|--------|
|        |        |
| ON     | (ON)   |
| 1-3    | 1-2    |

(ON) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4  
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A 48VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. HARDWARE SUPPLIED: O-RING AND HEXNUT
13. INGRESS RATING: IP40
- ▲ 14. LAMP VOLTAGE: 2.8V

|     |        |                            |         |     |
|-----|--------|----------------------------|---------|-----|
| E   | 23614  | update +/- Terminals       | 2/27/19 | MW  |
| D   | 23363  | UPDATED RATING TO 2A 48VDC | 5/11/18 | MJR |
| C   | 22886  | UPDATED RATING TO 1A 24VDC | 6/19/17 | MJR |
| REV | PCR NO | DESCRIPTION                | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE PV3H2B0BB-341

SCALE 3:2

DATE 1/14/2015

DR rc

DWG 52-PV3H2B0BB341

REV E