

RECEPTACLE HOUSING 4 WAY

APTIV P/N

CODING

13543925

CODING - A

SCALE 2:1

13543926

CODING - B






SCALE 2:1

13543927

CODING - D

SCALE 2:1


SECTION A - A



NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAQE XXXX/XXX
2	FEMALE CONNECTOR ACCORDING TO: - TEMPERATURE CLASS TX - ENGINE VIBRATOR CLASS VX - SEALING CLASS EX
3	USER'S MANUAL: 13543928-CUS74-S01
4	DELIVERY CONNECTOR WEIGHT : SEE TABLE
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
7	MATERIAL NAME
8	TOOL CAVITY NUMBER
9	INDEX REPLCEMENT INSERT
10	PART CAVITY NUMBER
11	SUPPLIER LOGO
12	REPLACEMENT INSERT BLANK
13	DATE INSERT

DWG STATUS				ZONE	REVISION HISTORY			AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG	INITIAL RELEASE				P.BAL	M.LAG	M.LAG
20DE21	R	01									

3D VIEW



SCALE 1:1

DWS TYP	
CUSTOMER PART DRAWING	
WEIGHT (GRI)	DISTR CODE
SEE TABLE	D
VOLUME (CM³)	
ROUTING	

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:
ISO1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

• APTIV •
CONNECTION SYSTEMS
Chennai, India
COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

DR	P.BALAJI	DATE	20DE21
APVD1	LAGUETTE MAURICE		20DE21
APVD2	LAGUETTE MAURICE		20DE21
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

MATERIAL
SEE TABLE

DRAWING NAME
RECEPTACLE HOUSING 4 WAY
FOR MTS/MOS 0.63

DRAWING NUMBER
13543928

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	01	

OVERALL DIMENSION FOR MOUNTABILITY

SECONDARY LOCKING
IN END LOCKED POSITION

WITH MATING PART

MOUNTING OPENING

SCALE 2:1

SCALE 2:1

ASSOCIATED PARTS (FOR INFORMATION)					
DESCRIPTION	APTIV P/N	WIRE SECTION	DIAMETER OF WIRE SIZE		
MATING PART	-	-	-		
FEMALE TERMINAL MTS 0.63	13580658	0.75mm²	1.9		
RECEPTACLE HOUSING 4 WAY	D	13543927	0.00058	PA66 GF15	VIOLET
	B	13543926	0.00058	PA66 GF15	NATURE
	A	13543925	0.00058	PA66 GF15	BLACK
DESCRIPTION	CODE	APTIV PART NUMBER	WEIGHT (kg)	MATERIAL	COLOR

☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)									CHART E	
☐ DIM FOR HELP	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400
		0	30	70	100	150	200	250	300	400	
	TOLERANCE UNLESS OTHERWISE SPECIFIED										
☐ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	
ANGULAR TOLERANCE ±2°											

