








NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAQE TBD
2	FEMALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS TX -ENGINE VIBRATOR CLASS VX -SEALING CLASS EX
3	USER'S MANUAL: 13543894-CUS74-S01
4	DELIVERY CONNECTOR WEIGHT : SEE TABLE
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
△	MATERIAL NAME
△	TOOL CAVITY NUMBER
△	INDEX REPLACEMENT INSERT
△	PART CAVITY NUMBER
△	SUPPLIER LOGO
△	REPLACEMENT INSERT BLANK
△	DATE INSERT

DWG. TYP	CUSTOMER PART DRAWING
WEIGHT (GR)	SEE CHART
VOLUME (CM³)	---
ROUTING	---
UNLESS OTHERWISE SPECIFIED	

GENERAL TOLERANCES ACCORDING TO:	SEE CHART
GD&T ACCORDING TO:	ISO 1101

REFERENCE	
FIRST ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	

• APTIV •			
CONNECTION SYSTEMS Chennai, India COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.			
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.			
DR	P.BALAJI	DATE	18N021
APVD1	LAGUETTE MAURICE		18N021
APVD2	LAGUETTE MAURICE		18N021
APVD3			
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001			
MATERIAL			
SEE TABLE			
DRAWING NAME			
RECEPTACLE HOUSING 2 WAY FOR MQS 0.63			
DRAWING NUMBER			
13543894			
SIZE	SCALE	FRAME NO	SHEET NO
A1	5:1	1 OF 1	1 OF 1
STG	REV	N/P	
R	01		



ASSOCIATED PARTS (FOR INFORMATION)						
DESCRIPTION	APTIV P/N	WIRE SECTION	DIAMETER OF WIRE SIZE			
MATING PART	13543904	-	-			
MQS 0.63 FEMALE TERMINAL	-	0.75mm²	1.9			
RECEPTACLE HOUSING 2 WAY	D	1	13543893	0.0067	PBT GF10	VIOLET
	C	1	13543891	0.0067	PBT GF10	BLUE
	A	2	13605737	0.0067	PBT GF10	YELLOW
	A	2	13605736	0.0067	PBT GF10	BLACK
	A	1	13543888	0.0067	PBT GF10	YELLOW
DESCRIPTION	A	1	13543887	0.0067	PBT GF10	BLACK
	CODE	VERSION	APTIV PART NUMBER	WEIGHT (kg)	MATERIAL	COLOR

○ DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART	E1
FROM	> 0	> 20	> 30
TO	> 20	> 30	> 70
			> 100
			> 150
			> 200
			> 250
			> 300
			> 400
1 DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED		
	±0.15	±0.2	±0.3
	±0.4	±0.5	±0.6
	±0.8	±1	±1.2
□ THEORETIC DIM	ANGULAR TOLERANCE ±2°		

