











SECTION A-A



NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAQE TBD
2	FEMALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS TX -ENGINE VIBRATOR CLASS VX -SEALING CLASS EX
3	USER'S MANUAL: 13543918-CUS76-S01
4	DELIVERY CONNECTOR WEIGHT : SEE TABLE
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
7	MATERIAL NAME
8	TOOL CAVITY NUMBER
9	INDEX REPLACEMENT INSERT
10	PART CAVITY NUMBER
11	SUPPLIER LOGO
12	REPLACEMENT INSERT BLANK
13	DATE INSERT

3 DWG STATUS				2 REVISION HISTORY				1 AUTH DR APVD 1 APVD 2			
DATE	STG	REV	N/P/CHG	ZONE							
17DE21	R	01			INITIAL RELEASE				P.BAL	M.LAG	M.LAG

3D VIEW



SCALE 1:1

DWG. TYP CUSTOMER PART DRAWING	
WEIGHT (GR)	DISTR CODE
SEE TABLE	
VOLUME (CM³)	

ROUTING	

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART


GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

• APTIV •			
CONNECTION SYSTEMS Chennai, India COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.			
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.			
DR	P.BALAJI	DATE	17DE21
APVD1	LAGUETTE MAURICE		17DE21
APVD2	LAGUETTE MAURICE		17DE21
APVD3			
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001			
MATERIAL SEE TABLE			
DRAWING NAME RECEPTACLE HOUSING 3 WAY FOR MTS/MQS 0.63			
DRAWING NUMBER 13543918			
SIZE	SCALE	FRAME NO	SHEET NO
A1	5:1	1 OF 1	1 OF 1
		STG	REV N/P
		R	01



ASSOCIATED PARTS (FOR INFORMATION)					
DESCRIPTION	APTIV P/N	WIRE SECTION	DIAMETER OF WIRE SIZE		
MATING PART	-	-	-		
FEMALE TERMINAL MTS 0.63	13580658	0.75mm²	1.9		
RECEPTACLE HOUSING 3 WAY	D	13543917	0.00048	PBT GF10	VIOLET
	B	13543915	0.00048	PBT GF10	NATURE
	A	13543914	0.00048	PBT GF10	BLACK
DESCRIPTION	CODE	APTIV PART NUMBER	WEIGHT (kg)	MATERIAL	COLOR

DIM TO CHECK	DIMENSIONAL RANGE (MM)											
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	CHART
1) DIM FOR HELP	TO	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400		
TOLERANCE UNLESS OTHERWISE SPECIFIED												
ANGULAR TOLERANCE ±2°												

