













ASSOCIATED PARTS				
PART DESCRIPTION	PART NUMBER	MVL PART NUMBER	WIRE SIZE (mm²)	AWG
DCK 1.5 FEMALE TERMINAL	Sn PLATED	33405736	-	22
	Au PLATED	13898605	F427200	
	Sn PLATED	13609029	60002031	20-17
	Au PLATED	13609492	60002034	
	Ag PLATED	35268997	-	
	Sn PLATED	13647358	60002041	17-15
	DCK 1.5 SWS (GRAY)	33318278	-	22
	DCK 1.5 SWS (LIGHT GRAY)	33318279	-	20-18
	DCK 1.5 SWS (BLACK)	33318275	-	17-15
	DCK 1.5 CAVITY PLUG (DARK GRAY)	35020635	-	-

DIN ISO 2768	Tolerance Class medium (m)					
Linear Dimensions except for broken edges	Permissible deviations for basic size range (mm)					
	0.5 *1 up to 3	over 3 up to 6	over 6 up to 30	over 30 up to 120	over 120 up to 400	over 400 up to 1000
	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8
Broken edges (radii, chamfers)	Permissible deviations for basic size range (mm)					
	0.5 *1 up to 3		over 3 up to 6			over 6
		±0.2		±0.5		±1
	Permissible deviations for ranges of lengths, in mm, of the shorter side of the angle concerned					
Angular dimensions	up to 10	over 10 up to 50	over 50 up to 120	over 120 up to 400	over 400	
	±1°	±0° 30'	±0° 20'	±0° 10'	±0° 5'	
*1) For nominal sizes below 0.5mm, the deviations shall be indicated adjacent to the relevant nominal sizes!.						

4	INTERFACE SEAL	SILICONE RUBBER	RED	35198315	I	I
3	FEMALE TPA	PA6-GF 30	BLUE	35198312	I	I
2	FEMALE HOUSING CODE B	PA6-GF30	BLACK	35200478	X	I
1	FEMALE HOUSING CODE A	PA6-GF 30	BLACK	35198311	I	X
REF	DESIGNATION	MATERIAL	COLOR	DELPHI P/NO	QTY	

INTENTIONAL RANGE (mm)	SCALE
FROM > 0 TO 20	> 20
20 TO 30	> 30
30 TO 40	> 40
40 TO 50	> 50
50 TO 60	> 60
60 TO 70	> 70
70 TO 80	> 80
80 TO 90	> 90
90 TO 100	> 100
100 TO 120	> 120
120 TO 150	> 150
150 TO 200	> 200
200 TO 250	> 250
250 TO 300	> 300
300 TO 400	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED	
ANGULAR TOLERANCE 12°	

DWG. TYPE PART DRAWING	DISTR. CODE D
WEIGHT (LBS)	
VOLUME (LBS)	
ROUTING	
UNLESS OTHERWISE SPECIFIED	
GENERAL TOLERANCES ACCORDING TO:	
OD&T ACCORDING TO:	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	

• APTIV •	
CONNECTION SYSTEMS	
Oremat, India	
COPYRIGHT 2018 APTIV, ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR: KANG, DONG-JU	DATE: 30MY18
APVD1: KANG, DONG-JU	30MY18
APVD2: SEO, JU-WON	30MY18
APVD3: PARK, JOO-HYUN	30MY18
APVD4:	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (104900)	
MATERIAL:	
SEE NOTES	
DRAWING NAME: DCK1.5 8WAY FEMALE CONNECTOR ASSEMBLY	
DRAWING NUMBER: 35200475	
SIZE: A0	SCALE: 5:1
FRAME NO: 1	SHEET NO: 1
STG REV: R 01	NVP