







ASSOCIATED PARTS			DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
N°	DESIGNATION	APTIV PN	DATE	STG	REV	N/P	CHG						
1	PLUG 800	35098453	17AP19	R	01	-			INITIAL RELEASE		P.K.S	E.LAM	J.FAB



SECTION A-A



3D VIEW
SCALE 1:1



• APTIV •

CONNECTION SYSTEMS
Chennai, India

COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

CE PLAN EST LE PROPRIETE DE DELPHI CORPORATION ET CONTIENT DES INFORMATIONS DELPHI CONFIDENTIELLES. LA REPRODUCTION, LA DISTRIBUTION ET L'UTILISATION DE CE DOCUMENT OU DE SES DONNEES MATHÉMATIQUES CAO, AINSI QUE LA COMMUNICATION DE TOUT CONTENU À AUTRUI, SANS AUTORISATION EXPRESSE EST INTERDITE.

DR		DATE
PRAVEEN KUMAR.S		17AP19
E.LAM		17AP19
M.VENARD		17AP19
J.FABRE		17AP19
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
MATIERES PROSCRITES ET CONTENU RECYCLABLE SEION DELPHI 10949001

MATERIAL
SEE TABLE

DRAWING NAME

REAR SEALING ASSEMBLY
35093966-CUS03

DRAWING NUMBER

35093966

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	-

DWG TYP		DISTR CODE D
PART DRAWING		
WEIGHT (GR)	30.6 +/- 10%	
VOLUME (CM³)	----	
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE TABLE

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.

LA LIGNE TRACÉE SUR LA RÉFÉRENCE PIÈCE INDIQUE QUE LA PIÈCE N'EST PAS DISPONIBLE À LA COMMANDE.

LES RÉFÉRENCES PIÈCES QUI NE SONT PAS BARRÉES INDICENT QUE CELLES-CI SONT DISPONIBLES PHYSIQUEMENT POUR ÊTRE COMMANDÉES.

CONTACTER LE SERVICE COMMERCIAL DE APTIV POUR S'ASSURER DE LA DISPONIBILITÉ DES PIÈCES.

R 0.2 MAX R 0.1 MAX

SHARP CORNER TOLERANCE

DIM TO CHECK COTES À VÉRIFIER	DIMENSIONAL RANGE (MM)											CHART E
	FROM TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400		
☐ DIM FOR HELP COTES POUR INFO	TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐ THEORETIC DIM COTES THÉORIQUES		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE ±2°												

N°	DESCRIPTION		WIRE SECTION		MATERIAL	SECTION VIEW
			35mm ²	50mm ²		
	REAR SEALING ASSEMBLY	APTIV PN	35099247	35099248		
1	RETAINER	APTIV PN	35098819	35098818	PA66 GF30	
		COLOR	BLACK	BROWN		
		SIZE (D2) ± 0.2	14.7	15.9		
		SIZE (D3) ± 0.2	17.6	18.9		
2	SWS	APTIV PN	35098464	35098461	SILICON	
		COLOR	BLUE	GREY		
		SIZE (D1) ± 0.2	13	14.4		