









①





NOTES	
-	ON MAIN VIEW ASSEMBLY 33341403 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269104-CUS71 - PRELIMINARY ASSEMBLY 35269104-CUS72 - HARNESS ASSEMBLY 35269103-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 7 WAY 1.5/2.8 FEMALE CONNECTOR ASM DWG-NO.: 35153947 - BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35428682 (HT DWG-NO.: 17-2271-001-CSG)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1.0MM ² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION: - TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40 - 2.8 TERMINAL DWG-NO.: 13548085 MAX WIRE CROSS SECTION: 2.5MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK
8	INTERFACE FOR CLIP MOUNTING HT CLIP NUMBER: YCCSFT6.5PT0.8-2.5; FT6LG.M.St.Aufn.II

POSITION	1				2				3			
NAME	HOUSING STRAP MOUNT				SECONDARY LOCK				SL SEAL			
MATERIAL	PBT GF30 FR17				PBT GF30				LSR 50 SHORE			
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	
PART-NO.:	33338787	33338780	33338536	33338534	33345107	33347359	33347309	33347314	33282488	33344859	33283927	
-	---	---	---	---	---	---	---	---	---	---	---	
-	1	---	---	---	---	---	---	---	1	---	1	
-	---	1	---	---	---	---	---	---	1	---	1	
-	---	---	1	---	---	---	---	---	1	---	1	
-	---	---	---	1	---	---	---	---	1	---	1	
-	---	---	---	---	1	---	---	---	---	1	1	
-	---	---	---	---	---	1	---	---	---	1	1	
-	---	---	---	---	---	---	1	---	---	1	1	
-	---	---	---	---	---	---	---	1	---	1	1	

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P/CHG						
19NO18	R	01			INITIAL RELEASE		P.BAL	P.NAJ	M.GRU
29MR19	R	01	AA	B7 A7	REFERENCE HELLERMANN TYTON DWG-NO. ADDED CLIP REFERENCE CHANGED		K.FAR	M.GRU	K.PIT
27OC20	R	01	AB	B7 69 B7	PROTECTION CAP APTIV DWG-NO.: 35428682 WAS 35274876 PART AVAILABILITY FOR PART NUMBERS 33346260, 33347854, 33347853, 33347852 UPDATED NOTES UPDATED		P.NAJ	M.GRU	

SCALE
1:1



DWG. TYPE PART DRAWING		DISTR. CODE D
WEIGHT (GR)	SEE CHART	
VOLUME (CM ³)	---	
ROUTING		
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO: SEE CHART		
GD&T ACCORDING TO: ISO 1101		
REFERENCE		
FIRST ANGLE PROJECTION 		
DO NOT SCALE CAD  NIX		
USE MATH DATA		

• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.
TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI, BEZ NADANIA WYRAŹNYCH UPRAWNIEN, JEST ZABRONIONE.

	DATE
DR	P.BALAJI
APVD1	P.NAJDUCH
APVD2	M.GRUDZEWSK
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA APTIV 10949001

MATERIAL
SEE CHART

DRAWING NAME
7 WAY 1.5 / 2.8
CTCS STRAP MOUNT MALE ASSEMBLY

DRAWING NUMBER
35153956

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AB

C

B

A

DIM TO CHECK	DIMENSIONAL RANGE (MM)											
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	CHART
1) DIM FOR HELP	TO	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400		
TOLERANCE UNLESS OTHERWISE SPECIFIED												
THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE ±2°												

