


Mobile TV Stand - Height Adjustable, 13" to 42" TVs and Monitors, Locking Casters, Black

MODEL NUMBER: DMC1342S



Height-adjustable rolling TV cart lets you move your flat-panel display smoothly and safely from one room to another.

Features

Move Your Flat-Panel Display Wherever Your Audience Is DMC1342S combines a height-adjustable TV stand with the convenience of a rolling cart. Mount your flat-panel television or monitor to this mobile TV stand, and then roll it safely and smoothly from room to room or from one corner of the room to another. It is recommended for classrooms, trade shows, lecture halls, offices, auditoriums, conference rooms, hotels and other settings where you need your TV or monitor to be mobile. The scratch-resistant powder-coated finish tolerates frequent handling and blends easily into any décor.

Raise, Lower, Swivel and Tilt the Screen to Find the Most Comfortable Viewing Angle The height-adjustable mobile TV floor stand fits most LCD, plasma and other flat-panel displays from 13 to 42 inches. Its durable aluminum and steel frame supports up to 44 pounds (19.9 kg). You can raise or lower the height of the display from 29.5 to 48.9 inches above the floor. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features 30° tilt and 3° to +3° swivel. The durable steel frame withstands the stress of repeated adjustments.

Rolls Easily from Place to Place on Sturdy Locking Metal Casters The mobile TV cart with wheels rolls almost effortlessly to the proper viewing location and angle on sturdy swivel casters with rubber wheels that move smoothly in any direction through doorways and over thresholds. The rear casters lock to keep the stand securely in position while at rest.

VESA-Compliant Mounting Ensures Display Compatibility VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 75 x 75, 100 x 100, 200 x 100 and 200 x 200. Mounting hardware is included.

Specifications

OVERVIEW	
UPC Code	037332248855
Device Compatibility	Monitor/HDTV

Highlights

- Ideal for rolling your flat-panel TV through classrooms, trade shows, offices and lobbies
- Raise and lower the height of the display from 29.5 to 48.9 in. for comfortable viewing
- Rolling TV stand offers -3° to +3° swivel and 30° tilt to help you find the perfect angle
- Durable steel construction blends into any room décor and supports up to 44 lbs (19.9 kgs)

Applications

- Show videos in a multipurpose area, such as a hotel lobby or lecture hall, where a permanent display is impractical
- Move a flat-screen monitor into a meeting room or office for web conferencing
- Create temporary digital signage in an auditorium or trade show
- Roll your television into a secure area for storage when not in use

Package Includes

- DMC1342S Mobile TV Stand, 13" to 42" TVs and Monitors
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	100x100; 200x100; 200x200; 75x75
Motion	Tilt
Mounting Location	Floor
Degrees of Motion	0° to +10°
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	42
Maximum Screen Size (cm)	106.7
Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20
Number of Displays	1
Shipping Dimensions (hwd / in.)	32.70 x 7.30 x 3.50
Shipping Dimensions (hwd / cm)	83.06 x 18.54 x 8.89
Shipping Weight (lbs.)	14.60
Shipping Weight (kg)	6.62
Unit Dimensions (hwd / in.)	48.800 x 19.800 x 17.900
Unit Dimensions (hwd / cm)	124.0 x 50.2 x 45.4
Unit Weight (lbs.)	13.9
Unit Weight (kg)	6.30
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No
Pre-Installed Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.