


Medical-Grade Temperature Sensor for Healthcare Power Modules, 2 ft. (0.6 m)

MODEL NUMBER: HCTHERMISTOR



Medical temperature sensor connects to Tripp Lite power module to prevent overcharging, detect shorted cells and prolong battery life.

Features

Medical-Grade Temperature Sensor Protects Connected Battery from Excessive Heat This medical temperature sensor provides extra fault protection for the sealed lead acid (SLA) batteries in your HC150SL or HCINT150SL power module for mobile medical carts. The HCTHERMISTOR lets the power module shut down battery charger if the battery's temperature exceeds 50 degrees Celsius (122 degrees Fahrenheit). It helps prevent overcharging, which can protect the connected battery and prolong its lifespan.

Compatible with Medical Power Modules Connect the RJ45 end of the two-foot medical-grade temperature sensor cable to the temperature sensor port on your power module. The other end is a ring terminal that connects to the battery's negative post.

Highlights

- Monitors battery temperature to help prevent overcharging and protect battery life
- Ends connect to RJ45 battery temperature port and battery's negative terminal
- Shuts down battery charger if battery temperature exceeds 50°C

Applications

- Monitor temperature of a power module's SLA battery to ensure it doesn't exceed 50°C and endanger its lifespan

Package Includes

- HCTHERMISTOR Medical-Grade Temperature Sensor, 2 ft.

Specifications

OVERVIEW	
UPC Code	037332164575
Accessory Type	Temperature Sensor
Accessory Class	UPS Accessories
PHYSICAL	
Cable Length (ft.)	2
Cable Length (m)	0.61
Cable Length (in.)	24
Cable Length (cm)	299.72
Shipping Dimensions (hwd / in.)	5.28 x 1.26 x 1.18



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	5.000 x 0.500 x 0.500
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.