

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/ST), 7M (23 ft.)

MODEL NUMBER: **N318-07M**



Highlights

- Premium 62.5/125 duplex (zipcord) fiber patch cable - 7 m
- Ideal for LAN applications
- Glass fiber composition
- LC/ST connectors

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/ST connectors

Package Includes

- 7-meter duplex MMF LC/ST 62.5/125 fiber cable

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 7-meters/Connectors: 2 LC/ST connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are 10-ft. (3.05 m) or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

| OVERVIEW | |
|----------------------|------------------|
| UPC Code | 037332139511 |
| Technology | Multimode |
| Optical Mode | OM1 |
| CONNECTIONS | |
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side B - Connector 1 | ST DUPLEX (MALE) |
| Endface Polish | PC |



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|---------------------------------|---------------------------------|
| Cable Jacket Color | Orange |
| Connector Color | Black; Gray |
| Cable Jacket Material | LSZH |
| Cable Jacket Rating | OFNR |
| Clad Diameter (microns) | 125 |
| Core Diameter (microns) | 62.5 |
| Number of Fibers | 2 |
| Cable Length (ft.) | 23 |
| Cable Length (m) | 7.01 |
| Cable Length (in.) | 275.6 |
| Minimum Bend Radius | 20 mm (Dynamic); 10 mm (Static) |
| Shipping Dimensions (hwd / in.) | 0.10 x 6.10 x 7.10 |
| Shipping Dimensions (hwd / cm) | 0.25 x 15.49 x 18.03 |
| Shipping Weight (lbs.) | 0.10 |
| Shipping Weight (kg) | 0.05 |
| Fiber Cable Length | 7M (23 ft) |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 5% to 85% RH, Non-Condensing |
| Storage Humidity Range | 35% to 65% RH, Non-Condensing |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit); 10 Gbps |
| Attenuation @ 850NM | 3.0 dB/km |
| Insertion Loss | LC 0.20 dB; ST 0.20 dB |
| FEATURES & SPECIFICATIONS | |
| Push/Pull Tabs | No |
| Breakout | No |
| Trunk | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

| | |
|--|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.