


P.C. MOUNTING






▲ O.P. (MM)	P.T. (MM)
8.80 ± 0.8	1.60 MAX.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- ▲ 3. RATING: 3A @125VAC
1.5 A @ 250VAC UL
- OPERATING FORCE: 30 ± 10 GRAMS
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- CONTACT RESISTANCE: 100 Milli-OHMS MAX.
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGING: 1,000 PER BAG.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-102032	PRINT UPDATE	07/03/23	JS	TITLE SS0750301F030P1A				000021344
					SCALE	DATE	DR	DWG	REV
					4:1	11/11/2009	BLR	Q971028	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED