






RECOMMENDED
PANEL CUT OUT



▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
OFF	N/A	ON
OPEN	N/A	1-3

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.5
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY
4. ELECTRICAL LIFE: 6,000 CYCLES
5. OPERATING TEMP: 0°C to 85°C
6. CONTACT RESISTANCE: 50mΩ MAX. INITIAL
7. INSULATION RESISTANCE: 2MΩ AT 500VDC
8. DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT RATING: 20A 125VAC,
15A 277VAC
2HP 125/277VAC
- ▲ 11. SUPPLIED HARDWARE: 2 HEXNUTS



REV	ECO NO	DESCRIPTION	DATE	BY					OBJECT ID
D	ECO-102074	SWITCH FUNCTION POS 1 CHANGED TO OPEN	07/14/23	JS	TITLE ST121D02				000001061
					SCALE	DATE	DR	DWG	REV
					1:1	6/19/2017	MW	34-ST121D02	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED