





RECOMMENDED PANEL CUT-OUTS

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
1-2	NONE	2-3

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 16(8)A 125/250VAC μ T125/55
- ELECTRICAL LIFE: 6,000 CYCLES
- CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
- DIELECTRIC STRENGTH: >1,500V AC 1MIN
- INSULATION RESISTANCE: >100MOHMS
- OPERATING TEMP: -10°C to 125°C
- INGRESS PROTECTION: IP40
- ▲ DENOTES CRITICAL PARAMETER.
- SUPPLIED HARDWARE: TOOTH WASHER AND TWO HEXNUTS.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100172	NEW RELEASE	06/16/21	MR	TITLE ST5SP81T2C2				100116993
					SCALE	DATE	DR	DWG	REV
					2:3	5/17/2021	MJR	14-ST5SP81T2C2	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED