




NOTES:


1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @ 50VDC
- ▲ 5. OPERATING FORCE: 160 ± 50 gf
6. TRAVEL: 0.25 +0.20/-0.10 mm
7. CONTACT RESISTANCE: 100 MILLI-OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: SILVER
10. ▲ DENOTES CRITICAL PARAMETER.
11. OPERATING TEMP: -40°C to 85°C



▲ CAP COLOR: RED
p/n Q800302
(1RRED)



▲ SWITCH
p/n P010205
(TL1105JAF160Q)



TITLE TL1105JAF160Q1RRED

A	24715	CREATE "P" PRINT	1/28/21	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 4:1	DATE 1/26/2021	DR MW	DWG XP0241P	REV A
--------------	-------------------	----------	----------------	----------