






P.C.B. LAYOUT






CIRCUIT: SPST ▲

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50VDC, 50mA
- ▲ 5. OPERATING FORCE: 100 ± 50 gf
6. TRAVEL: 0.3 ± 0.15 mm
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: SILVER
10. ▲ DENOTES CRITICAL PARAMETER
11. OPERATING TEMP: -40°C TO 85°C



▲
ACTUATOR
COLOR: BROWN



C	24550	REMOVE STEP IN HOUSING, CHANGE TEMP	10/19/20	JM
B	18742	LEG TOLERANCE WAS +/- 0.1	12/22/09	BLR
A	14189	RELEASED FOR PRODUCTION	7/27/04	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE TL1105XF100Q

SCALE 4:1

DATE 12/22/2009

DR BLR

DWG P020231

REV C