




NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 50mA @ 12 VDC
6. CYCLE LIFE: 100,000 MAKE-AND-BREAK CYCLES
7. INSULATION RESISTANCE: 100 M Ω MIN.
8. DIELECTRIC STRENGTH: 250 V RMS
9. CONTACT RESISTANCE: 100m Ω MAX.
10. OPERATING TEMP.: -25°C to 70°C
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LED COLOR: YELLOW
13. TRAVEL: 0.25 $\pm$ 0.10mm
14. ACTUATION FORCE: 350 $\pm$ 100 gf
- ▲ 15. PACKAGE: CAPS WILL BE BAGGED SEPERATELY - 1,000 PER BAG
- ▲ 16. CAPS TO BE ASSEMBLED ONTO THE SWITCH AFTER SOLDERING BY THE END USER.



LED PARAMETER	FORWARD CURRENT	FORWARD VOLTAGE @ 20mA	LUMINOUS INTENSITY
UNITS	mA	V	mcd
YELLOW	20	2.1 TYP. - 2.6 MAX.	715 TYP.



E-SWITCH®

B	24033	UPDATED NOTE 15. PACK...	9/10/19	MJR
A	23751	NEW RELEASE	1/23/19	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL6275BA2PQTY

SCALE 3:1

DATE 1/23/2019

DR MJR

DWG T062794

REV B