



*Quality Products. Service Excellence.*

## Thick-Wall Plastic Enclosures w/ EMI/ RFI Shielding **1594R Series**

EMI/ RFI Copper Conductive Coating Inside

### Key Features:



- Rugged electronic instrument enclosures, ideally suited for mounting printed circuit boards.
- Heavy duty, thick wall design with an average wall thickness of .13" (3.3 mm).
- Molded from flame retardant ABS plastic (material carries a UL flammability rating of 94V-0).
- Interior of each enclosure part is specially masked and sprayed with an RFI/EMI copper conductive coating (see photo above).
- Coating manufacturer specifies an attenuation of more than 75 db from 1 Mhz. to 1 Ghz.
- Designed to meet IP54.
- Countersunk lid is secured with four M3 x 0.5 - 0.71" (18 mm) long, Philips machine screws threaded into integral brass bushings. Perfect for applications with repetitive assembly and disassembly are required.
- Stocked in black with matte textured finish.



For non-shielded applications, try series 1594 (general purpose and water-tight options)



### Enclosures

Part Number	Color	Length	Width	Enclosure Depth (Less Lid)
1594RABK	Black	56	56	28
1594RBBK	Black	81	56	28
1594RCBK	Black	104	66	33
1594RDBK	Black	132	66	43
1594REBK	Black	168	107	53

Tags: plastic, ABS, heavy duty, thick wall, multipurpose, PCB, copper coated, EMI, RFI, shielded

*Data subject to change without notice*

