


PANEL CUTOUT

PANEL THICKNESS	X
1.50 - 2.00mm	30.2
2.00 - 3.00mm	30.4





SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3, 5-6	OPEN	2-1, 5-4



CIRCUIT: DPDT

NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER PLATED COPPER
5. CONTACT RATINGS: 20A @ 125VAC [cURus]
20A @ 250VAC [cURus]
2HP 125/250VAC [cURus]
18(12)A 250V~5E4 (TUV)
6. CONTACT RESISTANCE: 50m Ω MAX. INITIAL
7. INSULATION RESISTANCE: 500M Ω MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
9. IP RATING: IP55
10. OPERATING TEMPERATURE: -20°C to 65°C [cURus]
11. ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-101345	print update	10/31/22	MW	TITLE WB246D112S				000001128
					SCALE	DATE	DR	DWG	REV
					1:1	12/10/2010	CB	34-WB246D112S	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED