

## Features

- Super Fast Reverse Recovery Time
- Glass Passivated Junction
- Low Profile Package
- Low Thermal Resistance
- Lead Free Finish/RoHS Compliant (Note 1)("P" Suffix Designates RoHS Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free. "Green" Device (Note 2)
- Moisture Sensitivity Level 1



## Maximum Ratings @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Value			Unit
		UG1DHL	UG1GHL	UG1JHL	
Peak Repetitive Reverse Voltage	$V_{RRM}$	200	400	600	V
Working Peak Reverse Voltage	$V_{RWM}$				
DC Blocking Voltage	$V_R$				
RMS Reverse Voltage	$V_{RMS}$	140	280	420	V
Average Rectified Forward Current @ $T_L=115^\circ\text{C}$	$I_{F(AV)}$	1			A
Non-Repetitive Peak Surge Current @ 8.3ms Half Sine Wave	$I_{FSM}$	30			A
Current Squared Time @ $1\text{ms} \leq t \leq 8.3\text{ms}$	$I^2t$	3.735			$\text{A}^2\text{s}$

## Marking code

Part Number	Marking code
UG1DHL	UG1D
UG1GHL	UG1G
UG1JHL	UG1J

## Internal Structure


Pin	Description	Simplified outline	Graphic symbol
1	Cathode	 XXXX = Marking code	
2	Anode		

Note:

1. High temperature solder exemption applied, see EU directive annex 7a.
2. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


# 1 Amp Super Fast Recovery Rectifier 200 to 600 Volts

## SOD-123HL



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.074	0.086	1.88	2.18	
B	0.146	0.157	3.70	4.00	
C	0.041	0.053	3.19	3.61	
D	0.024	0.036	1.05	1.35	
E	0.087	0.102	0.61	0.91	
F	0.016	0.031	2.20	2.60	
G	0.012	0.000	0.40	0.80	
H	0.012		0.30		REF
I	0.004	0.012	0.10	0.30	
J	0.033	0.045	0.85	1.15	
K	0.000	0.012	0.00	0.30	
L	0.006	0.018	0.15	0.45	

## Suggested Solder Pad Layout



## Thermal characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$T_J$	Operating Junction Temperature Range		-55		150	°C
$T_{stg}$	Storage Temperature Range		-55		150	°C
$R_{th(J-L)}$	Thermal Resistance from Junction to Lead	Note 1		20		°C/W
$R_{th(J-A)}$	Thermal Resistance from Junction to Ambient	Note 1		80		°C/W

Note:

1. Mounted on P.C.B. with 5mm\*5mm copper pad areas,  $R_{th(J-L)}$  is measured at the terminal of cathode band.

## Electrical Characteristics @ 25°C Unless Otherwise Specified

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage UG1DHL UG1GHL UG1JHL	$V_F$	$I_F=1A; T_J=25^{\circ}C$			0.92 1.25 1.70	V
Reverse Current	$I_R$	at Rated $V_R; T_J=25^{\circ}C$ at Rated $V_R; T_J=125^{\circ}C$			5 100	$\mu A$
Reverse Recovery Time UG1DHL~UG1GHL UG1JHL	$t_{rr}$	$I_F=0.5A; I_R=1.0A;$ $I_{rr}=0.25A; T_J=25^{\circ}C$			25 35	nS
Junction Capacitance UG1DHL UG1GHL UG1JHL	$C_J$	$V_R=4V; f=1MHz; T_J=25^{\circ}C$		17 15 16		pF

## Curve Characteristics

Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Forward Characteristics




Fig. 4 - Typical Forward Characteristics




Fig. 5 - Typical Forward Characteristics






Fig. 6 - Typical Reverse Leakage Characteristics



## Curve Characteristics

Fig. 7 - Typical Capacitance Characteristics



## Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:2.5Kpcs/Reel

## \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

## \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

## \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.