


SPECIFICATIONS:

MATERIALS:	
CONTACT:	BRASS
PLATING:	SEE P/N TABLE BELOW
AMPERAGE:	5A MAX



PART NUMBER	PLATING	WIRE AWG RANGE
170-002-170L001	GOLD FLASH ON MATING AREA // NICKEL ON WIRE CRIMP AREA	20-28 AWG
170-002-170L002	10μ" GOLD OVER 50μ" NICKEL ENTIRE CONTACT	20-28 AWG
170-002-170L003	30μ" GOLD OVER 100μ" NICKEL ENTIRE CONTACT	20-28 AWG

NOTE: CONTACTS SUPPLIED ON 10,000/pc REEL

NORCOMP CRIMP TOOL PART NUMBER => 170-701-170-000

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.



DRAWN:
PAM JENKINS
DATE:
05/28/2002

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1	OF 2	REV 6
DWG NO.	170-002-170L00Y		



DETAIL A

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS
	DATE: 05/28/2002

NorComp

SCALE: NTS	SHEET 2 OF 2	REV 6
DWG NO. 170-002-170L00Y		