DESCRIPTION: FEMALE // D-SUB CRIMP CONTACT // LOOSE

SPECIFICATIONS:

MATERIALS:
CONTACT: BRASS
PLATING: SEE P/N TABLE BELOW
AMPERAGE: 5A MAX

Ø2.10±0.05

Ø1.70<sup>+0.05</sup>

PART NUMBER	PLATING	WIRE AWG RANGE
170-102-170L001	GOLD FLASH ON MATING AREA //	20-28 AWG
	NICKEL ON WIRE CRIMP AREA	
170-102-170L002	10μ" GOLD OVER 50μ" NICKEL	20-28 AWG
	ENTIRE CONTACT	20-20 AVVG
170-102-170L003	30μ" GOLD OVER 100μ" NICKEL	20-28 AWG
	ENTIRE CONTACT	

NOTE: CONTACTS SUPPLIED IN BAGS OF 500/pcs

NORCOMP CRIMP TOOL PART NUMBER => 170-701-170-000

RoHS COMPLIANT

体

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION

DRAWN:
PAM JENKINS
DATE:

05/28/2002

1.65±0.05

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1	_
DWC NO		-

170-102-170L00Y

REV