

DESCRIPTION: SOLID BARREL MICRO-D // SOLDER CUP // FEMALE

SPECIFICATIONS:



MATERIALS:
INSULATOR: PBT, UL94 V-0, BLACK
CONTACTS: 15µ" GOLD PLATED BRASS
SHELL: NICKEL PLATED ZINC ALLOY 60µ"-100µ"

ELECTRICAL:
RATED CURRENT: 2A
RATED VOLTAGE: 60VDC
D.W.V.: 6000 VAC for 1 min.
INSULATION RESISTANCE: 1000 MOhms MIN.
CONTACT RESISTANCE: 30 mOhms MAX.




ENVIRONMENT:
OPERATING TEMPERATURE: -40°C TO +85°C

WIRE AWG: 28 AWG MAX

*NOT DESIGNED TO MATE WITH NORCOMP 580-M & 581-M SERIES CONNECTORS.
**DESIGNED TO MATE WITH NORCOMP 380 // 381 SERIES CONNECTORS.



NESTED
SOLID BARREL
CONTACT



DIMENSIONS(mm)

SIZE	A	B	C	D	E
9	19.55	14.35	5.08	3.81	8.70
15	23.36	18.20	8.89	7.62	12.40
25	29.70	24.55	15.24	13.97	19.00

380-YYY-203L001
SERIES 380 = SOLDER CUP MICRO-D
POSITIONS 09, 15, 25
GENDER 1 = FEMALE SOLID BARREL CONTACTS
SOLDER CUP TERMINATION
CONTACT PLATING OPTIONS 1 = 15u" GOLD PLATING

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: J. KADEL
DATE: 01/17/2025

TOLERANCES
.x ±0.20
.xx ±0.15
.xxx ±0.10
.xxxx ±0.05
ANGULAR ±1°

UNITS = mm

NorComp

DO NOT SCALE FROM DRAWING

SCALE: NTS
SHEET 1 OF 1
REV 2
DWG NO. 380-YYY-203L001