

DESCRIPTION: M12 MALE - CABLE MOUNT SOLDER CUP - 8 POS.

SPECIFICATIONS:

MATERIALS:





HOUSING:	PBT, UL94 V-0, BLACK
CONTACTS:	SEE P/N KEY BELOW
NUT:	SEE P/N KEY BELOW
SHELL:	TIN PLATED ZINC ALLOY
BACKSHELL:	NICKEL PLATED BRASS
ORING:	EPDM, BLACK

ELECTRICAL:

RATED CURRENT:	2A
RATED VOLTAGE:	30V
INSULATION RESISTANCE:	100 MOhms MIN.
CONTACT RESISTANCE:	10 mOhms MAX.

ENVIRONMENT:


OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67



0 = NO BACK SHELL INCLUDED
7 = Ø7.5mm BACK SHELL

3 = ZINC ALLOY/TIN (Z/T) SHELL & BRASS/NICKEL NUT
T = Z/T SHELL / 316 STAINLESS STEEL NUT

1 = GOLD FLASH PLATED BRASS CONTACTS
4 = 10µ" GOLD PLATED BRASS CONTACTS



858-008-103RLS4

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
03/07/2016

UNITS = inch[mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV 5

DWG NO.

858-008-103RLSY