

SPECIFICATIONS:

MATERIALS:

HOUSING:

PBT, UL94 V-0, BLACK 10μ" GOLD PLATED BRASS

CONTACTS:

NICKEL PLATED BRASS

NUT: SHELL: ORING:

NICKEL PLATED BRASS EPDM, BLACK

ELECTRICAL:

RATED CURRENT:

1.5A

RATED VOLTAGE:

30V

INSULATION RESISTANCE:

100 MOhms MIN.

CONTACT RESISTANCE:

10 mOhms MAX.

ENVIRONMENT:

WATER PROOF:

OPERATING TEMPERATURE: -40°C TO +85°C

IP67

MAX WIRE AWG:

26 AWG

THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DESCRIPTION: M12 // M // 17P ACODE // SOLDER CUP // REAR PANEL MOUNT

DATE:

12/11/2023

DO NOT SCALE FROM DRAWING SCALE:

NTS

SHEET 1 OF

REV

0

DWG NO.

859-017-103R004

NorComp