


FEMALE PLUG M12 STRAIGHT



NOTES:
RATED VOLTAGE: 3, 4 contacts 250V
5 contacts 60V
8 contacts 30V
RATED CURRENT: 3, 4, 5 contacts 4A
8 contacts 2A
PROTECTION CLASS: IP 67
TEMPERATURE: -25°C / +85°C

CONTACTS POSITION FRONT VIEW:

3 CONTACTS		4 CONTACTS		5 CONTACTS		8 CONTACTS	
PIN	WIRE	PIN	WIRE	PIN	WIRE	PIN	WIRE
1	BROWN	1	BROWN	1	BROWN	1	WHITE
2	---	2	WHITE	2	WHITE	2	BROWN
3	BLUE	3	BLUE	3	BLUE	3	GREEN
4	BLACK	4	BLACK	4	BLACK	4	YELLOW
5	---	5	---	5	GREY	5	GREY
						6	PINK
						7	BLUE
						8	RED
CODING REQUIRED TO IEC 61076-2-101							

FOR OPTIONS SEE - NUMERICAL CODE - ON SHEET 2

8	SEE MATRIX	ID CARRIER	PVC	TRANSPARENT
7	1	LABEL YELLOW	VINYL	---
6	-	CABLE	SEE SHEET 2	---
5	-	OVERMOLDING	TPU	SEE PART LIST
4	1	COUPLING NUT FEMALE	SEE PART LIST	SEE PART LIST
3	1	INSERT FEMALE BLACK	PUR	---
2	1	ORING RED	FPM	---
1	3 / 4 / 5	CONTACT M12 FEMALE	BRONZE	SELECTIVE Au OVER Ni
	8		BRASS	SELECTIVE Au OVER Ni
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

FUNCTIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

AS PER PCN#516775.

EC NO: 823996

DRWN: ANIKES1

CHK'D: GGA

APPR: GGA

2025/05/30

2025/05/30

2025/05/30

2025/05/30

INITIAL REVISION:

DRWN: JMARSZALEK

APPR: RSILLER

2016/01/11

2016/04/08

THIRD ANGLE PROJECTION

DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.05

1 PLACE ± 0.3

0 PLACES ± 0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

2:1

mm

A3-SIZE

120065

DOCUMENT NUMBER

1200651978

DOC TYPE

PSD

DOC PART

000

REVISION

A13

1 OF 4

10:55:41

2025/05/30

RELEASE DATE

P1

DOCUMENT STATUS

ENGINEERING NO. - NUMERICAL CODE (Available parts see PART LIST table. Others on request).

OPTIONS

80X000XXX

80=M12x1
Single ended

Contacts:
3=3 Contacts
4=4 Contacts
5=5 Contacts
8=8 Contacts

Heads style:
000=Plug Female Straight

Cable type: See Table

Units:
M=Meter






Length
Examples:
005=0.5 unit
010=1 unit
100=10 units

Overmold color:
Blank (Standard)=Black
A=Grey / G=Black / Y=Yellow

Coupling Nut:
Blank (Standard) & 3=Knurled Brass Ni Plated
1=Hexagonal Stainless steel
5=Knurled Derlin
7=Knurled Brass Ni Plated, Teflon Coated
9=Knurled / Hexagonal Brass Ni Plated

H= 2 pcs. of I/D Carrier PVC Transparent

COUPLING NUTS




CABLE INFORMATION (for more information see Cable Data Sheet).

CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE JACKET	UL	CSA	STATIC: TEMP. / BENDING RADIUS	DYNAMIC: TEMP. / BENDING RADIUS	DRAG CHAIN	SHIELD
E02	3 / 4 / 5 / 8	0.25mm²	PVC BLACK	UL 2464/1729	C22.2 I/II A/B 80°C/300V	-30°C to +80°C, 10xO.D.	-10°C to +80°C, 15xO.D.	-	-
E03	3 / 4 / 5	0.34mm²	PVC BLACK	UL 2464/1729	C22.2 I/II A/B 80°C/300V	-30°C to +80°C, 10xO.D.	-10°C to +80°C, 15xO.D.	-	-
H08	3 / 4 / 5 / 8	0.25mm²	PUR BLACK LS0H	UL 21198/10493	C22.2 I/II A/B 80°C/300V	-40°C to +80°C, 5xO.D.	-25°C to +80°C, 10xO.D.	2 000 000 cycles at 20°C, Temp. range +5°C to +60°C	-
H09	3 / 4 / 5	0.34mm²	PUR BLACK LS0H	UL 21198/10493	C22.2 I/II A/B 80°C/300V	-40°C to +80°C, 5xO.D.	-25°C to +80°C, 10xO.D.	2 000 000 cycles at 20°C, Temp. range +5°C to +60°C	-
P02	3 / 4 / 5 / 8	0.25mm²	PUR / PVC BLACK	-	-	-30°C to +80°C, 7xO.D.	-5°C to +80°C, 15xO.D.	-	-
P03	3 / 4 / 5	0.34mm²	PUR / PVC BLACK	-	-	-30°C to +80°C, 7xO.D.	-5°C to +80°C, 15xO.D.	-	-

CABLE LENGTH TOLERANCES

OVER	UP TO AND INCLUDING	TOLERANCES
0	305mm	+19mm
305mm	915mm	+45mm
915mm	1830mm	+56mm
1830mm	3660mm	+89mm
3660mm	7320mm	+165mm
7320mm	14640mm	+317mm
14640mm	30500mm	+610mm
30500mm	>	+2% of finished length



SCALE 1:1

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS		SCALE		CURRENT REV DESC: RETRACTED P/N 1200658191 AS PER PCN#516775.			molex		
FA = 0	mm	1:1								
FE = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)				CSE M12 XP AC FE STR XM SE UNSH					
FF = 0	ANGULAR TOL ± 1.0 °									
DIVISIONAL SYMBOLS	4 PLACES	±	EC NO: 823996 DRWN: ANIKES1 2025/05/30 CHK'D: GGA 2025/05/30 APPR: GGA 2025/05/30			PRODUCT CUSTOMER DRAWING				
	3 PLACES	±								
	2 PLACES	± 0.05								
	1 PLACE	± 0.3	INITIAL REVISION: DRWN: JMARSZALEK 2016/01/11 APPR: RSILLER 2016/04/08			DOCUMENT NUMBER 1200651978		DOC TYPE PSD	DOC PART 000	REVISION A13
	0 PLACES	± 0.5								
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING A3-SIZE	SERIES 120065	MATERIAL NUMBER SEE SHEET 3-4		CUSTOMER GENERAL MARKET	

A

Part No.	Engineering No.	Cable Length
1200658551	808000E02M1001	10m
1200658812	808000E02M150	15m
1200659256	808000E02M200	20m
1200659052	808000E02M2001	20m
1200658984	808000E02M2501	25m
1200659200	808000E02M250H	25m
1200659613	808000E02M300	30m
1200659053	808000E02M3001	30m
1200659187	808000E02M4001	40m
1200659387	808000E02M500	50m
8P H08 CABLE		
1200658642	808000H08M010	1m
1200658643	808000H08M015	1.5m
1200658644	808000H08M020	2m
1200658813	808000H08M025	2.5m
1200658645	808000H08M030	3m
1200658646	808000H08M040	4m
1200658244	808000H08M050	5m
1200658264	808000H08M100	10m
1200658930	808000H08M150	15m
1200658899	808000H08M250	25m
3P H09 CABLE		
1200659584	803000H09M003	0.3m
1200658637	803000H09M015	1.5m
1200658177	803000H09M100	10m
1200658636	803000H09M010	1m
1200658175	803000H09M020	2m
1200658638	803000H09M030	3m
1200658639	803000H09M040	4m
1200658176	803000H09M050	5m
4P H09 CABLE		
1200658891	804000H09M003	0.3m
1200658640	804000H09M010	1m
1200657395	804000H09M012	1.2m
1200658550	804000H09M015	1.5m
1200658178	804000H09M020	2m

FORMAT: master to prod-A3 REVISION: J1 DATE: 2021/05/09	10	9	8
---	----	---	---

