





COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



High power contacts are separately enclosed

5	2	High power contact	FMP020S117	30A / AWG 10-12
4	2	Signal contact	S/LR-K176 / Copper alloy	0.8µm Au
3	1	Shell	Steel	tin plated
2	1	Insulator rear part	PA (-55°C to +115°C) acc. UL94V-0	black
1	1	Insulator front part	PBT acc. UL94V-0	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
FUNCTIONAL SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0	DIMENSION UNITS	SCALE	MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-m	
	mm	2:1		
			CURRENT REVISION	
	4	24130	DRWN: DRAWN BY fvetter	25-09-2020
	3	23106	APPR: APPR BY fvetter	25-09-2020
	2	22167	INITIAL REVISION	
	1	21165	DRWN: DRAWN BY ADenzinger	30-11-2006
	REV.	CH.-NO.	APPR: APPR BY skusber	30-11-2006
	REPLACEMENT FOR:		FRIST ANGLE PROJECTION	DRAWING
			A3-SIZE	

molex		
FCT D-Sub Crimp Connector		
PRODUCT CUSTOMER DRAWING		
MATERIAL NUMBER		REVISION
1731070520		4
DOCUMENT NUMBER		SHEET NUMBER
FL7W2S7-1363		1 OF 1
CUSTOMER		
GENERAL MARKET		