


12		11		10		9		8		7		6		5		4		3		2		1	
LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS																			
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"	STOCK ±.001 [0.025] THICKNESS													
190560055	B-318-14	---	---	14	.265 [6.73]	.534 [13.56]	.554 [14.07]	1.115 [28.32]	---	.031 [0.79]													
190560057	B-318-38	---	---	38	.390 [9.91]																		
190560059	B-318-56	---	---	56	.328 [8.33]																		
190560063	B-323-04	---	---	4	.119 [3.02]	.250 [6.35]	.209 [5.31]	.639 [16.23]	.980 [24.89]	.031 [0.79]													
190560065	B-323-06	190560067	B-323-06T	6	.146 [3.71]																		
190560068	B-323-08	---	---	8	.173 [4.39]																		
190560070	B-325-10	---	---	10	.198 [5.03]	.467 [11.86]	.388 [9.86]	.916 [23.27]	.980 [24.89]	.031 [0.79]													
190560072	B-325-14	---	---	14	.265 [6.73]																		
190560075	B-325-56	---	---	56	.328 [8.33]																		
190560102	B-337-04	---	---	4	.119 [3.02]	.312 [7.92]	.285 [7.24]	.730 [18.54]	.980 [24.89]	.031 [0.79]													
190560104	B-337-06	---	---	6	.146 [3.71]																		
190560106	B-337-08	---	---	8	.173 [4.39]																		
190560109	B-337-10	---	---	10	.198 [5.03]	.342 [8.69]	.310 [7.87]	.775 [19.69]	---	.031 [0.79]													
190560114	B-339-06	---	---	6	.146 [3.71]																		
190560116	B-339-08	---	---	8	.173 [4.39]																		
190560118	B-339-10	---	---	10	.198 [5.03]																		



PARTS ON TAPE

- NOTES:
- MATERIAL: COPPER
PLATING: ELECTRO-TIN (.0003 MIN).
 - BRAZED SEAM
 - WIRE SIZE: 16-14 AWG
1.0-2.5 MM²
 - ALL DIMENSIONS IN INCHES/[MM].
 - PARTS ARE ROHS COMPLIANT.
 - DIMS. SHOWN ARE FOR REFERENCE ONLY.

NOTES:

① MAT'L: COPPER (STOCK TKN $\frac{.031}{.79}$)
PLATING: ELECTRO-TIN (.0003 MIN.)

② BRAZED SEAM


STUD SIZES: ($\pm .005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS = INCHES
M M

WIRE SIZE: 16-14 AWG
1.0-2.5 MM²



FILE NO.

B-CD-301-01

PART NUMBER	"W" $\pm .010$	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES	TITLE:
B-318-	$\frac{.534}{13.56}$	$\frac{.554}{14.07}$	$\frac{1.115}{28.32}$	10, 14, 56, 38	RING TONGUE TERMINAL
B-323-	$\frac{.250}{6.35}$	$\frac{.209}{5.31}$	$\frac{.639}{16.23}$	02, 04, 06, 08	VERSAKRIMP 300-SERIES
B-325-	$\frac{.467}{11.86}$	$\frac{.388}{9.86}$	$\frac{.916}{23.27}$	10, 14, 56	
B-337-	$\frac{.312}{7.92}$	$\frac{.285}{7.24}$	$\frac{.730}{18.54}$	04, 06, 08, 10	
B-339-	$\frac{.342}{8.69}$	$\frac{.310}{7.87}$	$\frac{.775}{19.69}$	04, 06, 08, 10	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED					SCALE: NTS
FRAC.	DEC.	ANG.	REFERENCE	DATE	DWG. NO.
$\pm$	$\pm$	$\pm$		11/28/84	A
				CHKD. BY: GZ	CUSTOMER DWG.
				APPRD. BY:	

ETC
INCORPORATED