


12		11		10		9		8		7		6		5		4		3		2		1	
LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS																			
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"	STOCK ±.001 [0.025] THICKNESS													
190560055	B-318-14	---	---	14	.265 [6.73]	.534 [13.56]	.554 [14.07]	1.115 [28.32]	---	.031 [0.79]													
190560057	B-318-38	---	---	38	.390 [9.91]																		
190560059	B-318-56	---	---	56	.328 [8.33]																		
190560063	B-323-04	---	---	4	.119 [3.02]	.250 [6.35]	.209 [5.31]	.639 [16.23]	.980 [24.89]	.031 [0.79]													
190560065	B-323-06	190560067	B-323-06T	6	.146 [3.71]																		
190560068	B-323-08	---	---	8	.173 [4.39]																		
190560070	B-325-10	---	---	10	.198 [5.03]	.467 [11.86]	.388 [9.86]	.916 [23.27]	.980 [24.89]	.031 [0.79]													
190560072	B-325-14	---	---	14	.265 [6.73]																		
190560075	B-325-56	---	---	56	.328 [8.33]																		
190560102	B-337-04	---	---	4	.119 [3.02]	.312 [7.92]	.285 [7.24]	.730 [18.54]	.980 [24.89]	.031 [0.79]													
190560104	B-337-06	---	---	6	.146 [3.71]																		
190560106	B-337-08	---	---	8	.173 [4.39]																		
190560109	B-337-10	---	---	10	.198 [5.03]	.342 [8.69]	.310 [7.87]	.775 [19.69]	---	.031 [0.79]													
190560114	B-339-06	---	---	6	.146 [3.71]																		
190560116	B-339-08	---	---	8	.173 [4.39]																		
190560118	B-339-10	---	---	10	.198 [5.03]																		



NOTES:

1. MATERIAL: COPPER

PLATING: ELECTRO-TIN (.0003 MIN).

2. BRAZED SEAM

3. WIRE SIZE: 16-14 AWG

1.0-2.5 MM²

4. ALL DIMENSIONS IN INCHES/[MM].

5. PARTS ARE ROHS COMPLIANT.

6. DIMS. SHOWN ARE FOR REFERENCE ONLY.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#512606.				molex						
INCH/mm		NTS												
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 764691 DRWN: RAVINR1 2023/08/31 CHK'D: GGA 2023/10/13 APPR: GGA 2023/10/13				RING TONGUE TERMINAL VERSAKRIMP 300-SERIES						
		MM	INCH											
4 PLACES	±		±	INITIAL REVISION:				DOCUMENT NUMBER 190560053				DOC TYPE PSD	DOC PART 000	REVISION A1
3 PLACES	±		± 0.005											
2 PLACES	±	0.13	± 0.01	DRWN: JJ 1984/11/28 APPR: JMACNEIL 2019/08/05				MATERIAL NUMBER SEE TABLE				CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1
1 PLACE	±	0.25	±											
0 PLACES	±		±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION 		DRAWING C-SIZE	SERIES 19056			
ANGULAR TOL ± 0.5 °														

NOTES:

① MAT'L: COPPER (STOCK TKN $\frac{.031}{.79}$)
PLATING: ELECTRO-TIN (.0003 MIN.)

② BRAZED SEAM


STUD SIZES: ($\pm .005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING # E32244
"CSA" LISTING # 18689

ALL DIMENSIONS = INCHES
M M

WIRE SIZE: 16-14 AWG
1.0-2.5 MM²



FILE NO.

B-CD-301-01

PART NUMBER	"W" $\pm .010$	"C" MIN.	"L" MAX.	REFERENCE	SCALE: NTS	DATE	TITLE:	AVAILABLE STUD SIZES
B-318-	$\frac{.534}{13.56}$	$\frac{.554}{14.07}$	$\frac{1.115}{28.32}$					10, 14, 56, 38
B-323-	$\frac{.250}{6.35}$	$\frac{.209}{5.31}$	$\frac{.639}{16.23}$					02, 04, 06, 08
B-325-	$\frac{.467}{11.86}$	$\frac{.388}{9.86}$	$\frac{.916}{23.27}$					10, 14, 56
B-337-	$\frac{.312}{7.92}$	$\frac{.285}{7.24}$	$\frac{.730}{18.54}$					04, 06, 08, 10
B-339-	$\frac{.342}{8.69}$	$\frac{.310}{7.87}$	$\frac{.775}{19.69}$					04, 06, 08, 10
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED FRAC. DEC. ANG.								
DRAWN BY: JJ CHKD. BY: GZ APPD. BY:								
RING TONGUE TERMINAL VERSAKRIMP 300-SERIES								
DWG. NO. A CUSTOMER DWG.								

ETC
INCORPORATED
molex