


10	9	8	7	6	5	4	3	2	1
MAT'L NO	ENG NO	STUD SIZE	"S" REF	"W" MAX	"L" REF				
191640840	SD-810	10	.214 (5.45)	.460 (11.68)	2.02 (51.3)				
191640884	SD-814	1/4	.278 (7.06)						
191640842	SD-8516	5/16	.340 (8.63)						
191640843	SD-838	3/8	.400 (10.16)	.616 (15.65)	2.18 (55.3)				
191641007	SD-812-XWP-PL	1/2	.520 (13.21)	.786 (19.96)	2.30 (58.3)				



NOTES:

- 1 TERMINAL: TIN PLATED COPPER.
- 2 INSULATION: HEAT SHRINKABLE TUBING WITH HOT MELT ADHESIVE LINER. COLOR: RED
- 3. MWID = MAXIMUM WIRE INSULATION DIAMETER.
- 4. MUST BE RoHS COMPLIANT

FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{C} = 0$ $\frac{F}{D} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REDRAWN TO NX, "L" DIM WAS MAX			<b>molex</b>						
	INCH/MM		NTS											
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
	4 PLACES		±	MM	±	INCH	EC NO: 800326 DRWN: DEANNM1 2024/09/24 CHK'D: ETHRODAHL 2024/10/11 APPR: ETHRODAHL 2024/10/11 INITIAL REVISION: DRWN: BENDERLE 2004/02/24 APPR: RDEROSS 2004/03/01			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
	3 PLACES		±	MM	±	SD-19164-066				PSD	001	D		
	2 PLACES		±	MM	±									
1 PLACE		±	MM	±										
0 PLACES		±	MM	±										
ANGULAR TOL		±	°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER			
							B-SIZE	19164		GENERAL MARKET	1 OF 1			