



SWITCH SPECIFICATIONS	
POLE - POSITION	1P1T
CONTACT RATING	0.5A 12V DC
CONTACT RESISTANCE	200mΩ MAX.
INSULATION RESISTANCE	100 MΩ min. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable ; 1024 V AC for 1 Minute
OPERATING FORCE	160±50gf
OPERATING LIFE	500,000 cycles
OPERATING TEMPERATURE RANGE	-40°C ~ 85°C
TOTAL TRAVEL	0.2±0.1

LED SPECIFICATIONS							
 ATTENTION LEDs are Electrostatic Sensitive devices 	Unit	Value / LED Color					
		Blue 5mA	Pure Green	Red	Yellow	Orange	Green
LUMINOUS INTENSITY @20mA I _v	mcd						
Dominant Wavelength λD	nm						
FORWARD VOLTAGE@20mA V _f	V						

■ A single bin cannot be ordered, please contact us in advance if you need a particular bin sorting before placing your order to clarify the lead time, MOQ and pricing

u HOW TO ORDER

TC009A	-	OPERATION N	POLE 1	POSITION 1	FORCE A	KNOB TYPE A	ACTUATOR A	LED F	-	CAP COLOR S	CAP SYMBOL See page 230,231
					A 160gf B 250gf			RGB Light F FULL COLOR		S SILVER (std) N GREEN R RED Y YELLOW G GRAY K BLACK □ WITHOUT	
								Two Color Light L1 L2 UB BLUE UB BLUE UG GREEN UG GREEN UR RED UR RED UY YELLOW UY YELLOW			K3 PK3 : Printing □ WITHOUT

