





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-24-213591	28JUN2024	RK	FJS



- WIRE RANGE 24-20 AWG.
 - INSULATION RANGE 1.02-2.03 [.040-.080] DIA.
 - FOR LOOSE PIECE PART SEE DWG 66594.
- ⚠ 0.76µm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27µm [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,
BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ⚠ TIN PLATED.
- ⚠ GOLD PLATING PER MIL-G-45204, TIN PER MIL-T-10727
- ⚠ 0.76µm [.000030] MIN PRECIOUS METAL PLATE IN LOCALIZED GOLD PLATE AREA,
1.27µm [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27µm [.000050] MIN NICKEL.
CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042,
BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).

OBSOLETE	REVERSE REELED FOR MINI-APPLICATOR	⚠	1-66584-0
	REVERSE REELED FOR MINI-APPLICATOR	⚠	66584-4
	-	⚠	66584-3
	REVERSE REELED FOR MINI-APPLICATOR	⚠	66584-2
	-	⚠	66584-1
DESCRIPTION		FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. FURLER 09JUN2003	TE Connectivity		
		CHK G. STEINHAUER 09JUN03			
		APVD G. STEINHAUER 09JUN03	NAME		
		PRODUCT SPEC	CONTACT, SOCKET, STRIP TYPE VI, MULTIMATE		
		APPLICATION SPEC	-		
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-66584
CUSTOMER DRAWING		SCALE 6:1	SHEET 1 OF 1	REV E	