



P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI9442	02JAN2007	AM	RDR
	A	REVISED PER ECR-21-000055	14JAN2021	AP	IG



7. BREAKAWAY FUNCTION OCCURS AT AN AXIAL LOAD OF 50 TO 100 LBS.

6. THIS CONNECTOR MATES WITH HD34-24-91P\*-\*\*\*\*\*  
(\* = SEAL TYPE, \*\*\*\*\* = ALL MODIFICATIONS) AND HDBOX24-91P\*.

5. CAVITY 5 IS WITH CONTACT SIZE 16 AND THE GROMMET IS SEALED.

4. CONTACTS 4 AND 5 ARE INTERNALLY CONNECTED. (BUILT-IN BRIDGE)

3. FOR CONTACTS AND WIRES PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

2. FOR PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-016-0000.

1. CONSULT THE FACTORY FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. MALAGON 28DEC2006	TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK B. BYFORD 02JAN2007			
		APVD R. REED 02JAN2007	NAME BREAKAWAY PLUG BAYONET COUPLING CONNECTOR 24-91 ARR. HDB SERIES HDB SERIES		
		PRODUCT SPEC 108-151014			
		APPLICATION SPEC 114-151014			
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-HDB36-24-91SX
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1	REV A