

KILOVAC EV200P Series Latching Contactor With 1 Form X (SPST Latch) Contacts Rated 500+ Amps, 12-900 Vdc

Product Facts

- Latching version of popular EV200 Series
- Designed to be the smallest, lowest cost, lightest weight sealed contactor in the industry at its current rating
- Optional auxiliary contacts for monitoring position of power contacts
- Hermetically sealed — operates in explosive/harsh environments with no oxidation or contamination of coil or contacts during long periods of non-operation
- Not position sensitive, can be mounted in any orientation
- RoHS versions available



Physical Data

Contact Arrangements —
Main Contacts — SPST, Latching
Auxiliary Contacts 1 — Up to 2 Form A
Dimensions — See drawing
Weight, Nominal — .95 lb. (.43 kg)

Environmental Data

Shock, 11ms 1/2 Sine (Operating) — 30 G_{peak}
Sine Vibration, 20 G_{peak} —
55-2000 Hz
Random Vibration, 14.06 Grms —
15 Hz (.002 G²/Hz), 100 Hz (.002 G²/Hz),
450 Hz (.12 G²/Hz), 900 Hz (.12 G²/Hz),
2000 Hz (.083 G²/Hz)
Operating Temperature Range —
-40°C to +85°C

Electrical Data

Voltage Rating —
Main Contacts (Max) — 750 Vdc
Current Rating, Continuous —
Main Contacts 2 — 500A
Contact Resistance —
Main Contacts 3 —
0.2 mΩ max above 300A
0.3 mΩ max between 50 and 300A
Hot Switching Performance (Positive Polarity) 4 —
200A make/ break @ 270Vdc —
10,000 cycles
600A make/ break @ 360Vdc —
100 cycles
800A break only @ 360Vdc —
15 cycles
2000A break only @ 360Vdc — 1 cycle
Mechanical Life (Min) —
75,000 cycles

Dielectric Withstand Voltage —
Terminal to Terminal/ Terminals to Coil —
1mA max @ 2,200 Vrms

Insulation Resistance —
Terminal to Terminal/ Terminals to Coil —
100MΩ min @ 500Vdc new
50MΩ min @ 500Vdc end of life

Coil Data 5

Nominal Coil Voltage 6 — 12 Vdc

Pick Up/Latch (Max) @ 25°C —
9 Vdc

Hold (Min) — N/A

Reset (Max)/Dropout (Min) —
9 Vdc

Duty Cycle, Max 7 — 20%

Coil Resistance @ 25°C — 2.5 Ω

Operate Specs @ 25°C

Operate Time (Typ) — 15 ms
Operate Bounce (Max) — 7 ms
Release Time (Max) — 15 ms

Notes:

- Product can be configured alternately with form B or C auxiliary switches if required. This changes the product part number, depending on specific auxiliary configuration. Consult TE for availability and part number
- Ambient conditions and conductor design affect rating. Terminal temperature rise should be 75°C max above ambient. Keep relay terminals below 150°C max continuous, 175°C max for two hours, and 200°C for 1 minute.
- Stabilized reading. Contact resistance may exceed spec in the first 10 minutes of current carry.
- Units are polarity sensitive. Approximately 50% de-rating for reverse polarity switching. Consult factory for review of specific requirements.
- Over temperature range unless noted. Suggested coil pulse = 50-100 ms.
- 24V and 48V coils available on request — consult factory.
- Intermittent Duty Coil. Coil overheating can occur if duty cycle

Ordering Information

Typical Part Number ►

Series: EV200 = 500+ Amp, 12-900VDC Contactor

Contact Form: P = Latching
F = Latching with 1 SPDT Aux.

Coil Voltage: 4 = 12 Vdc
5 = 24 Vdc
6 = 48 Vdc

Coil Terminations: A = 15.3 in. (300 mm)


Coil Termination Connector: N = None

Mounting & Power Terminals: A = Bottom Mount & Male 10mm x M8 Threaded Terminals

EV200 P 4 A N A

KILOVAC EV200P Series Latching Contactor (Continued)

Outline Dimensions



For factory-direct application assistance,
dial 800-253-4560, ext. 2055, or
805-220-2055.