



Electronic Stud Finder with Cross-Line Lasers



Electronic Stud Finder with Cross-Line Lasers detects hidden wood and metal studs with an auto deep scan of up to 1-1/2-Inch. The horizontal and vertical lasers can be used together or independently. Offering mutable audible alerts and bright LEDs across the top, it clearly indicates the full width of the stud. It features an ergonomic handheld grip, hold mode and withstands a 6.6-Foot (2 m) drop. Felt pads protect walls during use and bubble vial assists with alignment. Laser Class 3R; 25mW.

Specifications

Type:	Electronic	Application:	Detect Metal And Wood Studs Behind Walls, Center and Edge-Finding, Laser Leveling
Special Features:	Horizontal and Vertical Lasers; Felt Pads; Handheld Grip; Hold Mode; Mute Audible Tones	Magnetic:	No
Level Included:	Cross-Line Laser Levels; Bubble-Level	Laser Level Function:	Red Horizontal and/or Vertical Lines; 15' in All Directions
Laser Class:	Class 3R	Automatic Operation:	No
Audible Alert:	Yes	Detects Metal:	Yes
Detects Voltage:	No	Detects Live Wires:	No
Display:	(7) Bright Green LEDs	Scans Material:	Metal; Wood
Scan Depth:	Up to 1.5" (3.8 cm)	Overall Length:	7.63" (19.4 cm)
Overall Height:	4.5" (11.4 cm)	Overall Width:	2.75" (7 cm)
Material:	PC & PC-ABS Housing and Electronic Components	Drop Protection:	6.6' (2 m)
Batteries:	(2) AA (1.5V)	Included:	Stud Finder, 2x AA Batteries, Manual
Weight:	1 lb (0.47 kg)	Battery Type:	Alkaline
Laser mW:	25mW		