



CII

TE Internal #: 1-1617752-7

General Purpose Power Relay, AC, Polarized, Monostable, 2 Form C DPDT-CO, 10 A Contact Rating, 28 VAC Coil Voltage, Socket Mount, Hermetically Sealed

[View on TE.com >](#)

Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **2 Form C DPDT-CO**

Current Type: **AC**

Contact Current Rating: **10 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Contact Arrangement	2 Form C DPDT-CO
---------------------	------------------

Electrical Characteristics

Coil Current	.18 A
Contact Switching Voltage (Max)	115 VAC, 200 VAC
Contact Current Rating	10 A
Coil Voltage Rating	28 VAC

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Gold

Termination Features

Main Termination & Connection Type	Socket Pins
Coil Termination & Connection Type	Socket Pins

Mechanical Attachment



Product Mounting Feature Type	Mounting Brackets
Product Mount Type	Socket Mount

Usage Conditions

Operating Temperature Range	-70 – 125 °C[-94 – 257 °F]
Environmental Ambient Temperature (Max)	125 °C[257 °F]

Operation/Application

Vibration Resistance	30G's, 70 – 3000Hz
Shock Resistance	200G's, 6ms
Coil Magnetic System	Polarized, Monostable
Current Type	AC

Other

Contact Current Class	>5 – ≤10 A
-----------------------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 1617754
[FCA-410-1517M=M83536/15-017M](#)

Customers Also Bought



TE Part #1410714-2
[MULTIGIG RT GUIDE 7.2MM](#)



TE Part #9-1589788-2
[STM009PC2DM048Q = Wdualobe](#)




TE Part #8-1617349-0
[3SBM1089A2=M39016/36-006M](#)



TE Part #3-1617515-0
[3SBC1793A2=M39016/13-101M](#)



TE Part #5-1617800-8
[FCAC-150-KY4=50 AMP MID RANGE RELAY](#)



TE Part #070539-000
[TXR21AB90-1608AI](#)



TE Part #65053-234
[ELEC MODULE](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1617752-7_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1617752-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1617752-7_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

1-1617752-7

General Purpose Power Relay, AC, Polarized, Monostable, 2 Form C DPDT-CO, 10 A
Contact Rating, 28 VAC Coil Voltage, Socket Mount, Hermetically Sealed



Datasheets & Catalog Pages

5-1773450-5_sec5_FCA-210

English