



Mini-Circuits

MMIC SURFACE MOUNT


Power Splitter/Combiner

GP2S1+

2 Way-0° 50Ω 500 to 2500 MHz

FEATURES

- Very Wide Bandwidth, 500 to 2500 MHz
- Excellent Isolation, 20 dB typ.
- Excellent Amplitude Unbalance, 0.02 dB typ.
- Excellent Phase Unbalance, 0.9 deg. typ.
- Small Size, 0.118"x0.118"x0.035"
- High ESD Level
- Aqueous Washable



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Cellular
- GPS
- Radar
- WCDMA
- GSM
- Korea PCS

ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		500		2500	MHz
Insertion Loss* (above 3.0 dB)	500-2500		0.9	1.8	dB
Isolation	500-2500	9	20		dB
Amplitude Unbalance	500-2500	—	—	0.2	dB
Phase Unbalance	500-2500	—	—	5.0	deg.
VSWR (Port S)	500-2500	—	1.3	—	:1
VSWR (Ports 1,2)	500-2500	—	1.2	—	


* De-embedded from demo board loss.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating temperature	-40°C to 85°C
Storage temperature	-65°C to 150°C
Power Input (as a splitter)	1.5 W max.
Internal Dissipation	0.75 W max.

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
ECO-026464
GP2S1+
MCL NY
250806

PAGE 1 OF 3



Power Splitter/Combiner

GP2S1+

2 Way-0° 50Ω 500 to 2500 MHz

SUM PORT	2
PORT 1	7
PORT 2	9
GROUND	1,3,4,5,6,8,10,11,12, paddle

Top view of the package outline showing dimensions and features:

- Overall width: .196
- Overall height: .249
- Pin 1 location: .018 from left edge, .036 from bottom edge.
- Pin pitch: .096
- Pin diameter: .028, 3 PL.
- Trace width: .044, 3 PL. (SEE NOTE BELOW)
- Internal dimensions: .124, .028, .012 TYP, .047, .043, .023, TYP, .036, TYP, .004, .016, .009, .064, .021.
- Radius: R.344
- Features: 11X ϕ .020 PTH FOR GROUND, 3X ϕ .040, .006.
- Notes: SEE NOTE 3, PACKAGE OUTLINE.

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. SIGNAL RACES ARE NOT ALLOWED INSIDE HATCHED AREAS (APPROX. .030 X .030) AT 4 PLACES AS SHOWN.

A diagram showing a black rectangular block representing a black body. In the top-left corner of the block is a small white circle. An arrow points from the word "index" to this circle. Inside the block, the text "MCL GP2S XXXX" is written in white, stacked vertically. An arrow points from the text "model family designation" to this text.

TAPE & REEL INFORMATION: F66



Mini-Circuits

MMIC SURFACE MOUNT

Power Splitter/Combiner




GP2S1+

2 Way-0° 50Ω 500 to 2500 MHz

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR		VSWR 2
	S-1	S-2				S	1	
500	3.68	3.68	0.01	11.86	0.42	1.52	1.30	1.30
690	3.63	3.62	0.01	17.62	0.47	1.31	1.21	1.20
880	3.60	3.60	0.00	29.08	0.52	1.12	1.14	1.12
1070	3.64	3.65	0.01	26.49	0.66	1.10	1.09	1.07
1260	3.74	3.77	0.04	21.01	0.78	1.22	1.04	1.02
1450	3.84	3.88	0.04	20.24	0.87	1.30	1.07	1.05
1550	3.88	3.92	0.04	21.14	0.91	1.32	1.10	1.08
1640	3.91	3.94	0.03	22.91	0.97	1.30	1.14	1.11
1740	3.93	3.96	0.03	26.76	1.05	1.27	1.17	1.14
1830	3.95	3.97	0.02	34.69	1.16	1.22	1.20	1.17
1930	3.96	3.98	0.02	32.63	1.28	1.15	1.22	1.19
2020	3.98	3.99	0.01	24.55	1.41	1.08	1.24	1.21
2210	4.04	4.05	0.02	16.91	1.65	1.11	1.25	1.23
2400	4.16	4.19	0.03	12.90	1.80	1.34	1.24	1.24
2500	4.26	4.29	0.03	11.43	1.89	1.47	1.24	1.24

1. Total Loss = Insertion Loss + 3dB splitter loss.



ESD RATING

Human Body Model (HBM): Class 1A (250 to < 500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M2 (100V to < 250V) in accordance with ANSI/ESD STM 5.2 - 1999

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

