

2-2383519-1


✓ ACTIVE

AMP | Heavy Duty Sealed Connector Series

TE Internal #: 2-2383519-1

8 Position Housing, Housing for Male Terminals, Wire-to-Board /
Wire-to-Wire, Heavy Duty Sealed Connector Series[View on TE.com >](#)

Automotive Parts > Automotive Connectors > Automotive Housings



Connector & Housing Type: Housing for Male Terminals

Number of Positions: 8

Sealable: Yes

Operating Temperature Range: -40 – 140 °C [-40 – 284 °F]

Number of Rows: 2

Features**Product Type Features**

Mixed & Hybrid Connector	Yes
Connector Shape	Rectangular
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Primary Locking Feature	Clean Body
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	60 VDC
-------------------	--------

Body Features

Cable Exit Angle	180°, 90°
------------------	-----------

Primary Product Color	Gray
Connector & Keying Code	B

Contact Features

Contact Size	2.8mm, 5.8mm
Contact Type	Tab
Mating Tab Width	2.8 mm, 5.8 mm [.11 in] [.228 in]

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF30
Centerline (Pitch)	6 mm, 9 mm [.23 in] [.35 in]

Dimensions

Product Width	27 mm
Product Length	52.6 mm
Connector Height	50.6 mm

Usage Conditions

Operating Temperature Range	-40 – 140 °C [-40 – 284 °F]
Operating Temperature (Max)	140 °C [284 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

IP Rating	IP67, IP69K
Compatible With Agency/Standards Products	DIN IEC 512
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	120
Packaging Method	Bulk

Other

Serviceable	Yes
-------------	-----

Connector Position Assurance Capable No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | Heavy Duty Sealed Connector Series



Customers Also Bought



Documents

Product Drawings

8POS,AMP MCP 2.8,TAB HSG ASSY,SLD,COD B

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-2383519-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2383519-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2383519-1_A.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English