




TE Internal #: 2066046-3
Fuse Holder, Mini ATM Fuse, 2 Fuses (Maximum), 4 Position, 8.1 mm [.32 in] Centerline, Sealable, 25G, IP67, UL 94HB, Other Hard Wired Boxes
[View on TE.com >](#)

Automotive Parts > Automotive Power Distribution Boxes > Other Hard Wired Boxes



Component Type: Fuse Holder
Fuse Type: Mini ATM Fuse
Number of Fuses (Maximum): 2
Number of Positions: 4
Centerline (Pitch): 8.1 mm [.32 in]

Features

Product Type Features

Component Type	Fuse Holder
Fuse Type	Mini ATM Fuse
Sealable	Yes
Primary Locking Feature	Locking Lance

Configuration Features

Number of Fuses (Maximum)	2
Number of Positions	4

Body Features

Secondary Locking	No
-------------------	----

Contact Features

Contact Current Rating (Max)	20 A
------------------------------	------

Housing Features

Centerline (Pitch)	8.1 mm[.32 in]
--------------------	----------------

Usage Conditions



Operating Temperature (Max)	80 °C[176 °F]
Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]

Operation/Application

Vibration Class Level	25G
-----------------------	-----

Industry Standards

IP Rating	IP67
UL Flammability Rating	UL 94HB

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2066502-2
COVER 2 POS MINI FUSE BOX,MAT-2



TE Part # 1-2066502-4
COVER 2 POS MINI FUSE BOX,MAT-2



TE Part # 1579007-1
AUSDRUECKWERKZEUG



TE Part # 1-2066502-3
COVER 2 POS MINI FUSE BOX,MAT-2

Customers Also Bought



TE Part #CAT-AM705-CH8172
AMP MCP, SEALED CONNECTOR HOUSING



TE Part #1-2066502-2
COVER 2 POS MINI FUSE BOX,MAT-2



TE Part #1-2066502-4
COVER 2 POS MINI FUSE BOX,MAT-2




TE Part #2289990-1
BLIND PLUG,DIRECT CONNECTOR




TE Part #2290490-1
16POS,1.0 SERIES,REC HSG ASSY,SLD



TE Part #2373835-1
2POS,MQS,REC HSG ASSY,SLD,COD A



TE Part #2066043-2
12 POS. ECONOSEAL CAP HOUSING JMARK II+



TE Part #2312552-1
COVER,44P DIRECT CONNECTOR

Documents

Product Drawings

2 POS MINI FUSE BOX ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2066046-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2066046-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2066046-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

ICT Fuse and Relay Enclosures

English

Product Specifications

Application Specification

English