



Application Tooling > Heat Shrink Equipment



Equipment Processing Type: **Discrete**

Applicable Region: **Worldwide**

Heat Shrink Equipment Application: **In-Line Splice, Stub Splice**

Tooling Type: **Heating Tool**

Spare Parts Tooling Type: **RBK Processor**

Features

Product Type Features

Spare Parts Tooling Type	RBK Processor
--------------------------	---------------

Dimensions

Tubing Outer Diameter (Max)	≤ 19 mm[≤ .75 in]
Tubing Length (Max)	≤ 65 mm[≤ 2.56 in]

Product Availability

Applicable Region	Worldwide
-------------------	-----------

Other

Equipment Processing Type	Discrete
Heat Shrink Equipment Application	In-Line Splice, Stub Splice
Tooling Type	Heating Tool
Substrate Outside Diameter Max	9.5 mm

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
------------------------------	------------------




EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

<div>TE Part # 6-529533-1</div> <div>FIXTURE ID 4.5MM CPL.</div>	<div>TE Part # 7-2234788-3</div> <div>CABLE CLAMPER, CIRCLE</div>	<div>TE Part # 7-2234788-7</div> <div>KIT, TERMINAL HOLDER, RBK</div>	<div>TE Part # 7-2234788-4</div> <div>END CAP HOLDER, DUAL</div>
<div></div> <div>TE Part # 2234800-1</div> <div>RBK-X1 STD</div>	<div>TE Part # 8-529533-3</div> <div>DOUBLE FIXTURE ID 5.5MM</div>	<div>TE Part # 8-529533-4</div> <div>DOUBLE FIXTURE ID 8MM</div>	<div>TE Part # 6-529533-3</div> <div>FIXTURE ID 8MM CPL.</div>



TE Part # 6-529533-2 FIXTURE ID 5.5MM CPL.	TE Part # 2-2234788-9 HOLDER KIT, STUB TOOL	TE Part # 2234800-2 RBK-X1 CE STD	TE Part # 1-2234800-4 RBK-X1 CE, W/ AIR COOLING
TE Part # 4-2234788-7 CABLE FLATNESS KEEPER, RIGHT	TE Part # 7-2234788-1 CABLE CLAMPER, LEFT	TE Part # 4-2234788-9 END CAP HOLDER	TE Part # 7-2234788-0 STANDARD TOOL KIT
TE Part # 6-2234788-8 CABLE CLAMPER, FLATTEN	TE Part # 1-2234800-3 RBK-X1, W/ AIR COOLING	TE Part # 2384437-1 KIT, TERMINAL HOLDER, RBK	TE Part # 4-2234788-8 CABLE FLATNESS KEEPER, LEFT

Documents

Product Drawings  
RBK FIXTURE, CAP W/ FLATTEN BRKT, A/C  
English

- Instruction Sheets
- Instruction Sheet (non U.S.)  
English
  - Instruction Sheet (non U.S.)  
French
  - Instruction Sheet (non U.S.)
  - Instruction Sheet (non U.S.)
  - Instruction Sheet (non U.S.)
  - Instruction Sheet (non U.S.)
  - Instruction Sheet (non U.S.)
  - Instruction Sheet (non U.S.)  
German

