



| RUBBER PART GENERAL TOLERANCE |         |         |         |         |
|-------------------------------|---------|---------|---------|---------|
| PART DIM.                     | 1       | 2       | 3       | 4       |
| 0 TO 3                        | ± 0.2   | ± 0.3   | ± 0.4   | ± 0.5   |
| 3 TO 6                        | ± 0.2   | ± 0.4   | ± 0.5   | ± 0.6   |
| 6 TO 10                       | ± 0.3   | ± 0.5   | ± 0.6   | ± 0.8   |
| 10 TO 18                      | ± 0.3   | ± 0.6   | ± 0.8   | ± 1.0   |
| 18 TO 30                      | ± 0.4   | ± 0.8   | ± 1.0   | ± 1.5   |
| 30 TO 50                      | ± 0.5   | ± 1.0   | ± 1.5   | ± 2.0   |
| 50 TO 80                      | ± 0.6   | ± 1.2   | ± 2.0   | ± 2.5   |
| 80 TO 120                     | ± 0.7   | ± 1.4   | ± 2.5   | ± 3.0   |
| 120 TO 180                    | ± 0.8   | ± 1.6   | ± 3.0   | ± 4.0   |
| 180 TO 250                    | ± 1.0   | ± 2.0   | ± 4.0   | ± 5.0   |
| 250 TO 315                    | ± 1.2   | ± 2.5   | ± 5.0   | ± 6.0   |
| 315 TO 400                    | ± 1.5   | ± 3.0   | ± 6.0   | ± 7.0   |
| 400 TO 500                    | ± 1.8   | ± 3.5   | ± 7.0   | ± 8.0   |
| 500 OVER                      | ± 0.4 % | ± 0.8 % | ± 1.5 % | ± 2.0 % |



NOTE  
1) APPLICABLE PANEL DIMENSION  
HOLE DIA: ø32. THICKNESS: 0.7  
注 記  
1) 適用パネル寸法  
孔径: ø32, 板厚: 0.7

|     |      |          |          |        |     |     |          |     |      |
|-----|------|----------|----------|--------|-----|-----|----------|-----|------|
| LET | DATE | 98.04.02 | REVISION | RECORD | NEW | NO. | C98-T207 | M.O | CHKD |
|-----|------|----------|----------|--------|-----|-----|----------|-----|------|

| GENERAL TOLERANCE |                     |                   |        |        |
|-------------------|---------------------|-------------------|--------|--------|
| TOLMAX            | EQMAX               | 100MAX            | 250MAX | 2500VR |
| ANGLE             | ECCENT              | 0.1               | 0.1    | 0.1    |
| A                 | ±0.15               | ±0.2              | ±0.3   | ±0.5   |
| B                 | ±0.2                | ±0.3              | ±0.5   | ±0.75  |
| C                 | ±0.3                | ±0.5              | ±0.8   | ±1.0   |
| SPECIFIED         | RUBBER PART GENERAL | TOLERANCE CLASS 3 | MASS   | 10 #   |

|              |                   |                  |          |
|--------------|-------------------|------------------|----------|
| CUSTOMER     | CUSTOMER PART NO. | CUSTOMER DWG NO. | TREAT.   |
| OFFICE       | TRIAL PART NO.    |                  |          |
| VENDOR       | VENDOR NO.        |                  |          |
| DWG. TYPE    | DWG. SOURCE       | DWG. DATE        | UNIT     |
| R            | NEW               | 98.04.02         | mm       |
| APPROVED     | CHECKED           | DESIGN           | DRAWN    |
| N            | 佐藤                | 木村               | OSADA    |
| 1. TAKAMASHI |                   |                  |          |
| 98.04.03     | 98.04.03          | 98.04.03         | 98.04.03 |

|                    |                      |        |  |
|--------------------|----------------------|--------|--|
| MATL.              | 非耐熱弾性ゴマ(EPDM)        | TREAT. |  |
| SPEC.              | BLACK                | & FIN. |  |
| NAME               | WIPPER MOTOR GROMMET |        |  |
| PART NO.           | 7035-6813            |        |  |
| DWG NO.            | 7035-6813:R          |        |  |
| SET                | DWG NO.              |        |  |
| YAZAKI CORPORATION |                      |        |  |