


PART NO. AND CH. CODE	R ₁	R ₂	W ₁	W ₂	WIRE SIZE (mm ²)	WIRE DIAMETER	
						UNSEALED	SEALED
7114-4720-02	0.30	0.80	1.70	2.80	0.35	φ 1.10 ~ 1.70	φ 1.40 ~ 1.70
7114-4721-02	0.40	0.90	2.10	3.30	0.5 ~ 0.75	φ 1.40 ~ 2.20	φ 1.40 ~ 2.20



注記


1. 嵌合相手端子品番 : 7116-4720-02 ETC.

NOTES

1. MATING PART NO. : 7116-4720-02 ETC.



SEC. A-A



SEC. B-B

ISSUE MARK

										CUSTOMER				MATL. C2600 (t=0.20)				TREAT. & FIN.			
										CUSTOMER PART NO.				CUSTOMER DWG NO.				SPEC. TIN PLATING			
△	01.10.02	REVISED DIMENSION	C01-X984	N. S									NAME 0.64 SYSTEM CONNECTOR								
	01.03.30	NEW	C01-X348	N. S	OFFICE				TRIAL PART NO.												
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR								MALE TERMINAL								
GENERAL TOLERANCE										VENDOR NO.											
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO. 7114-4720-02 ETC.							
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	01.03.30	mm	5/1	3	CH. CODE							
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	DWG NO. 7114-4720-02:R								
©	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	Z1-Iskida Makoto				N. SUGIE		ISHIJIMA		SET DWG NO.					
SPECIFIED					MASS			9				01.10.10				01.10.02					
												00.12.07				01.10.02					
YAZAKI CORPORATION																					