



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Cavity Plug**
Cavity Diameter: **.64 mm [.025 in]**
Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**
Primary Product Color: **Natural**
Primary Product Material: **PBT GF**

Features

Product Type Features

Connector Seal & Plug Type	Cavity Plug
----------------------------	-------------

Body Features

Primary Product Color	Natural
Primary Product Material	PBT GF

Dimensions

Cavity Diameter	.64 mm[.025 in]
-----------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
Operating Temperature (Max)	125 °C[257 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	20000

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Generation Y Connector System](#)



Automotive Housings(138)



Automotive Seals & Cavity Plugs(6)



Automotive Signal & Power Connector Housings(138)

Customers Also Bought




TE Part #2-1393366-2
GET-SOCKET TERMINAL, SILVER VE



TE Part #1456867-3
PLG ASSY,2X8,UNSEALD, 0.64,Gen



TE Part #1924136-2
Carrier, 26P Generation Y, 52P Conn



TE Part #1924337-1
Shield Assembly, 54 POSN, 0.64mm BLK



TE Part #1924340-1
36P, 2 Row Carrier for 54P LAC



TE Part #2098633-1
40P Shield Assy, GY LAC




TE Part #2098634-1
Carrier, 20P, GY LAC, Black



TE Part #2-2236706-1
2-POS. SEALED 2.8MM USCAR
CLEAN BODY FOR



TE Part #2293333-1
16POS,GEN 50,REC HSG,ASSY



TE Part #2088128-5
HEIGHT GAUGE,HYBRID CONN

Documents

Product Drawings

CVTY PLUG,0.64 GENER. Y,CVTY DIA,MAT-SL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2377194-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2377194-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2377194-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English