




1

2

3




注記

1. 嵌合コルゲート・チューブの呼び径は、φ13とする。
2. 嵌合相手品番：7283-1407 ETC.

NOTES

1. MATING CORRUGATED TUBE'S DIAMETER IS CALLED "φ13".
2. MATING PART NO. : 7283-1407 ETC.

MATING CORRUGATED TUBE



(REFERENCE FIGURE)

GENERAL TOLERANCE

	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75					±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
©	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15

ISSUE MARK

CUSTOMER

CUSTOMER PART NO.

CUSTOMER DWG NO.

MATL.
SPEC.

PBT (BLACK)

TREAT.
& FIN.

NAME

090 II 10P SEALED CONNECTOR

REAR COVER FEMALE

PART NO.
CH. CODE

7134-4925-30

DWG NO.

7134-4925-30:R

SET DWG NO.

YAZAKI CORPORATION

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15

SPECIFIED

MASS

g

DWG TYPE

R

DWG SOURCE

NEW

DWG DATE

03/11/05

UNIT

mm

SCL

1:1

ANGLE

3

APPROVED

大佐

CHECKED

—

CHECKED

濱井

DESIGN

T. HAMAI

DRAWN

Y. IMAI

03.11.05

03.11.05

03/01/29

03/11/05

1

2

3